



## Schottky Barrier Rectifier

**Qualified per MIL-PRF-19500/553**

Qualified Levels:  
JAN, JANTX, JANTXV  
and JANS

### DESCRIPTION

This schottky barrier diode provides low forward voltage and offers military grade qualifications for high-reliability applications. This rugged DO-203AA rectifier is applicable for freewheeling diodes, rectification in high-frequency, low-voltage inverters, and for polarity protection.

**Important:** For the latest information, visit our website <http://www.microsemi.com>.

### FEATURES

- Internal solder bond construction.
- Hermetically sealed (welded).
- 600 Amps surge rating.
- JAN, JANTX, JANTXV and JANS qualifications are available per MIL-PRF-19500/553.
- RoHS compliant devices available by adding "e3" suffix (commercial grade only).

### APPLICATIONS / BENEFITS

- Metal and glass construction.
- Reverse energy tested.
- Fast recovery.

### MAXIMUM RATINGS @ $T_A = +25^\circ\text{C}$ unless otherwise stated

| Parameters/Test Conditions                                                                     | Symbol                  | Value       | Unit               |
|------------------------------------------------------------------------------------------------|-------------------------|-------------|--------------------|
| Junction and Storage Temperature                                                               | $T_J$ and $T_{STG}$     | -55 to +175 | $^\circ\text{C}$   |
| Thermal Resistance Junction-to-Case                                                            | $R_{\theta JC}$         | 2.0         | $^\circ\text{C/W}$ |
| Reverse Voltage, Repetitive Peak and Working Peak Reverse Voltage <sup>(1)</sup>               | $V_{RRM}$ and $V_{RWM}$ | 45          | V                  |
| Reverse Voltage, Nonrepetitive Peak                                                            | $V_{RSM}$               | 54          | V                  |
| Reverse Voltage <sup>(1)</sup>                                                                 | $V_R$                   | 45          | V                  |
| Forward Surge Current @ 8.3 ms half-sine wave                                                  | $I_{FSM}$               | 600         | A                  |
| Average Forward Current 50% duty cycle square wave @ $T_C = +125^\circ\text{C}$ <sup>(2)</sup> | $I_{FM}$                | 25          | A                  |
| Average Rectified Output Current @ $T_C = +125^\circ\text{C}$ <sup>(3)</sup>                   | $I_O$                   | 22.5        | A                  |
| Solder Pad Temperature @ 10 s                                                                  |                         | 260         | $^\circ\text{C}$   |

- NOTES:**
1. Full rated  $V_{RRM}$  and  $V_{RWM}$  with 50% duty cycle is applicable over the range of  $T_C = -55^\circ\text{C}$  to  $+165^\circ\text{C}$  for  $I_{FM} = 0$ . Full rated continuous  $V_R$  (dc) is applicable over the temperature range of  $T_C = -55$  to  $+155^\circ\text{C}$ . When  $V_R = 45$  V and  $T_C = +155^\circ\text{C}$ , then  $T_J = 175^\circ\text{C}$ .
  2. Average current with a 50 percent duty cycle square wave including reverse amplitude equal to the magnitude of full rated  $V_{RWM}$ . Derate linearly at  $0.625\text{ A}/^\circ\text{C}$  for  $T_C > +125^\circ\text{C}$ .
  3. Average current with an applied half-sine wave peak voltage value equal to the magnitude of full rated  $V_{RWM}$ . For temperature-current derating curves, see [Figure 4](#).



**DO-203AA (DO-4)  
Package**

#### **MSC – Lawrence**

6 Lake Street,  
Lawrence, MA 01841  
Tel: 1-800-446-1158  
(978) 620-2600  
Fax: (978) 689-0803

#### **MSC – Ireland**

Gort Road Business Park,  
Ennis, Co. Clare, Ireland  
Tel: +353 (0) 65 6840044  
Fax: +353 (0) 65 6822298


#### **Website:**

[www.microsemi.com](http://www.microsemi.com)

### MECHANICAL and PACKAGING

- CASE: Industry standard DO-4, (DO-203AA), 7/16" hex, stud with 10-32 threads, welded, hermetically sealed metal and glass.
- TERMINALS: Tin-lead plated or RoHS compliant matte-tin plating (commercial grade only) on nickel.
- POLARITY: Cathode to stud.
- MOUNTING HARDWARE: Nut, flat steel washer and lock washer available upon request.
- WEIGHT: Approximately 7.5 grams.
- See [Package Dimensions](#) on last page.

### PART NOMENCLATURE




### SYMBOLS & DEFINITIONS

| Symbol    | Definition                                                                                                                                                                            |
|-----------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| f         | Frequency                                                                                                                                                                             |
| $I_{FM}$  | Forward Current: The current flowing from the external circuit into the anode terminal. Also see first page ratings and test conditions for $I_{FM}$ with 50% duty cycle square wave. |
| $I_{FSM}$ | Surge Peak Forward Current: The forward current including all nonrepetitive transient currents but excluding all repetitive transients (ref JESD282-B).                               |
| $I_O$     | Average Rectified Forward Current: The output current averaged over a full cycle with a 50 Hz or 60 Hz sine-wave input and a 180 degree conduction angle.                             |
| $V_{FM}$  | Maximum Forward Voltage                                                                                                                                                               |
| $V_R$     | Reverse Voltage: A positive dc cathode-anode voltage below the breakdown region.                                                                                                      |
| $V_{RRM}$ | Repetitive Peak Reverse Voltage: The peak reverse voltage including all repetitive transient voltages but excluding all non-repetitive transient voltages.                            |
| $V_{RSM}$ | Non-Repetitive Peak Inverse Voltage: The peak reverse voltage including all non-repetitive transient voltages but excluding all repetitive transient voltages.                        |
| $V_{RWM}$ | Working Peak Reverse Voltage: The peak voltage excluding all transient voltages (ref JESD282-B). Also sometimes known historically as PIV.                                            |


**ELECTRICAL CHARACTERISTICS**

| Parameters / Test Conditions                                                                                                                                                                                                                                                                 | Symbol   | Min. | Max.                    | Typ. | Unit |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|------|-------------------------|------|------|
| Forward Voltage<br>$I_{FM} = 50 \text{ A}$ , $T_C = 25 \text{ }^\circ\text{C}$ *<br>$I_{FM} = 5 \text{ A}$ , $T_C = 25 \text{ }^\circ\text{C}$ *                                                                                                                                             | $V_{FM}$ |      | 0.68<br>0.50            |      | V    |
| Reverse Current Leakage<br>$V_{RM} = 45 \text{ V}$ , $T_J = 25 \text{ }^\circ\text{C}$<br>$V_{RM} = 45 \text{ V}$ , $T_J = 175 \text{ }^\circ\text{C}$ *<br>$V_{RM} = 45 \text{ V}$ , $T_J = 125 \text{ }^\circ\text{C}$ *<br>$V_{RM} = 45 \text{ V}$ , $T_C = -55 \text{ }^\circ\text{C}$ * | $I_{RM}$ |      | 1.5<br>220<br>40<br>1.5 |      | mA   |
| Junction Capacitance<br>$V_R = 5 \text{ V}$ , $f = 1 \text{ MHz}$ , $100 \text{ KHz} \leq f \leq 1 \text{ MHz}$                                                                                                                                                                              | $C_J$    |      | 2000                    |      | pF   |


\*Pulse test: pulse width 300  $\mu\text{sec}$ , duty cycle 2%

**GRAPHS**



**FIGURE 1**  
Typical Forward Characteristics




**FIGURE 2**  
Typical Reverse Characteristics

**GRAPHS**


**FIGURE 3**  
Typical Junction Capacitance



**FIGURE 4**  
Temperature - Current Derating Curve  
(Derate design curve constrained by the maximum rated junction temperature ( $T_J \leq 175^\circ\text{C}$ ) and current rating specified.)

**PACKAGE DIMENSIONS**


| Ltr             | Dimensions |       |             |       | Notes |
|-----------------|------------|-------|-------------|-------|-------|
|                 | Inch       |       | Millimeters |       |       |
|                 | Min        | Max   | Min         | Max   |       |
| C               |            | .250  |             | 6.35  | 5     |
| C <sub>1</sub>  | 0.018      | 0.65  | 0.46        | 1.65  | 5     |
| CD              | 0.265      | 0.424 | 6.73        | 10.77 | 6     |
| CH              | 0.300      | 0.405 | 7.62        | 10.29 |       |
| HF              | 0.403      | 0.437 | 10.24       | 11.1  | 6     |
| HT <sub>1</sub> | 0.075      | 0.175 | 1.91        | 4.45  | 7     |
| HT <sub>2</sub> | 0.060      | -     | 1.53        | -     | 7     |
| OAH             | 0.600      | 0.800 | 15.24       | 20.32 |       |
| SD              |            |       |             |       | 2     |
| SL              | 0.422      | 0.453 | 10.72       | 11.51 |       |
| SU              |            | 0.078 |             | 1.98  | 8     |
| UD              | 0.163      | 0.189 | 4.14        | 4.80  |       |
| ΦT              | 0.060      | 0.095 | 1.52        | 2.41  |       |

**NOTES:**

1. Dimensions are in inches. Millimeters are given for information only.
2. See "[mechanical and packaging](#)" for the polarity of the terminals.
3. Threads shall be 10–32 UNF–2A in accordance with FED–STD–H28. Maximum pitch diameter (SD) of plated threads shall be basic pitch diameter 0.1697 inch (4.31 mm).
4. Device shall not be damaged by a torque of 15 inch–pounds applied to a 10–32 UNF–2B nut assembled on thread.
5. The angular orientation and peripheral configuration of terminal 1 is undefined, however, the major surfaces over dimension C and C<sub>1</sub> shall be flat.
6. Dimension CD cannot exceed dimension HF.
7. A chamfer or undercut on one or both ends of the hex portion is optional; minimum base diameter at seating plane 0.403 inch (10.24 mm).
8. Length of incomplete or undercut threads UD.
9. In accordance with ASME Y14.5M, diameters are equivalent to  $\Phi x$  symbology.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microsemi:](#)

[1N6391](#)