




TOP VIEW




SIDE VIEW



BOTTOM VIEW



Specifications			Notes	Revision History													
Description	Value	Unit		Version	Description		Date	Approved									
Technology	Electro-Mechanical		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS	1	Released from Engineering		10/21/2013	J.S									
Resonant Frequency	2,048	(Hz)															
Rated Voltage	1.5	(V)															
SPL @ 10cm	75	(dBA)															
Coil Resistance	16	(ohm)															
Mount Type	Thru Hole																
Voltage Range	1 ~ 3	(V)															
Max Rated Current	30	(mA)															
Housing Material	NORYL																
Operating Temperature	-20 ~ +70	°C															
Storage Temperature	-30 ~ +80	°C															
Weight	2	(g)															
 DB UNLIMITED						Drawn by		Date		Checked by		Date		Approved by		Date	
						Electro-Mechanical Transducer			TE122001-7								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[TE122001-7](#)