

## Customer Part:



### Description

- Standard 2.5 x 2.0 oscillator in a ceramic package with a hermetically sealed metal lid.
- Model IQXO-793
- Model Issue number 1

### Frequency Parameters

- Frequency 27.0MHz
- Frequency Stability  $\pm 50.00\text{ppm}$
- Operating Temperature Range  $-40.00$  to  $85.00^\circ\text{C}$
- Ageing  $\pm 3\text{ppm}$  max per year

### Electrical Parameters

- Supply Voltage  $2.5\text{V} \pm 5\%$
- Current Draw  $10.000\text{mA}$

### Output Details

- Output Compatibility HCMOS
- Drive Capability  $15\text{pF}$
- Rise and Fall Time  $10.0\text{ns}$  max
- Duty Cycle 40/60%
- Output Voltage High: 90% of  $V_s$  min  
Output Voltage Low: 10% of  $V_s$  max

### Output Control

- Standby Function (pin1):  
No Connection = Output Enabled  
>70%  $V_s$  = Output Enabled  
<30%  $V_s$  = Output Disabled  
When disabled output goes to high impedance state
- Start Up Time:  $10\text{ms}$  max

### Noise Parameters

- Jitter (Phase 12kHz to 20MHz):  $1\text{ps}$  max
- Jitter (Period One Sigma):  $\pm 10\text{ps}$  typ
- Jitter (Period pk-pk):  $\pm 80\text{ps}$  typ

### Environmental Parameters


- Storage Temperature Range:  $-55$  to  $125^\circ\text{C}$
- Shock: MIL-STD-202, Method 213. Or comparable.
- Vibration: MIL-STD-883, Method 2007. Or comparable.

### Compliance


- RoHS Status (2015/863/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

### Packaging Details

- Pack Style: Reel Tape & reel in accordance with EIA-481D  
Pack Size: 3,000
- Alternative packing option available



### Outline (mm)



## Sales Office Contact Details:

UK: +44 (0)1460 270200  
Germany: 0800 1808 443

France: 0800 901 383  
USA: +1.760.318.2824

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)  
Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IQD Frequency Products:](#)

[LFSPXO056284Reel](#)