

Page
1 / 2

R F CHARACTERISTICS

FREQUENCY RANGE : 0 - 3 GHz
IMPEDANCE : 50 Ohms

FREQUENCY (GHz)	0 - 3
V.S.W.R <=	1.20
INSERT. LOSS <=	0.20 dB
ISOLATION >=	80 dB
AVER. POWER (*)	240 W

ELECTRICAL CHARACTERISTICS

ACTUATOR	: LATCHING
NOMINAL CURRENT AT 25° C (±10%)	: 420 mA
ACTUATOR VOLTAGE (Vcc)	: 12V (10 to 13V) / NEGATIVE COMMON
TERMINALS	: solder pins (250° C max./30 sec.)
INDICATOR RATING	: 1 W / 30 V / 100 mA
SELF CUT-OFF TIME	: 40 ms < CT < 120 ms
TTL INPUTS (E) - High level	: 2.2 to 5.5V / 800µA at 5V
- Low level	: 0 to 0.8V / 20µA at 0.8V

MECHANICAL CHARACTERISTICS

CONNECTORS	: SMA female	per MIL C 39012
LIFE	: 2.000.000	cycles
SWITCHING TIME (nominal voltage;25° C)	: < 10	ms
CONSTRUCTION	: splashproof	
WEIGHT	: <100	g


ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE RANGE (°C) : -40 , +85
STORAGE TEMPERATURE RANGE (°C) : -55 , +85


(* : average power at 25° C)

This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary

DRAWING



SCHEMATIC DIAGRAM



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

R585362300