

ISSUE 1; February 2018

Description

- IQXT-225 is a 2.0 x 1.6mm SMD Temperature Compensated Crystal Oscillator (TCXO) in a hermetically sealed package with E/D on pad 1 for low power operation.
- Developed frequencies: 16.368, 16.369, 19.2, 26.0, 33.6 and 38.4MHz



Frequency Parameters

- Frequency 16.368MHz to 38.4MHz
- Frequency Tolerance Max $\pm 1.50\text{ppm}$
- Frequency Stability $\pm 0.50\text{ppm}$
- Ageing $\pm 1\text{ppm}$ max per year @ 25°C
 $\pm 2^\circ\text{C}$
- Frequency Tolerance: @ 25°C $\pm 2^\circ\text{C}$ referred to nominal frequency before reflow soldering.
- Supply Voltage Variation (@ $\pm 5\%$ change): $\pm 0.1\text{ppm}$ max
- Load Variation (@ $\pm 10\%$ change): $\pm 0.1\text{ppm}$ max
- Reflow Variation (at 25°C $\pm 2^\circ\text{C}$ referred to frequency before reflow): $\pm 1\text{ppm}$ max, 24 hrs after reflow.

Electrical Parameters

- Supply Voltage 1.2V $\pm 5\%$
- Absolute Maximum Ratings:
Supply Voltage: -0.6V to 4.6V
E/D Control Voltage: -0.6V to Vs+0.6V (4.6V max)

Operating Temperature Ranges

- -30 to 85°C

Output Details

- Output Compatibility Clipped Sine
- Drive Capability 10k Ω /10pF $\pm 10\%$
- Output: DC coupled
Note: a 1000pF DC-cut capacitor is to be connected in the output line of the TCXO.
- Output Level: 0.8V pk-pk min
- Start Up Time: Vout $\geq 90\%$ of V pk-pk: 2ms max
- Start Up Time (within $\pm 0.5\text{ppm}$): 2ms max

Output Control

- Enable/Disable (pad 1):
Logic '1' (80%Vs min) or no connection to pad 1 enables the oscillator output.
Logic '0' (20%Vs max) to pad 1 disables the oscillator output, the output goes to a high impedance state.
Disable current in E/D mode: 3 μA max

Noise Parameters


- Phase Noise (typ): -135dBc/Hz @ 1kHz

Environmental Parameters


- Storage Temperature Range: -40 to 85°C

Manufacturing Details

- RoHS Terminations NiAu
- RoHS Reflow +250°C $\pm 10^\circ\text{C}$ for 10 sec max



Outline (mm)



Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: 0800 1808 443

France: 0800 901 383
USA: +1.760.318.2824

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com

Ordering Information

- *Minimum info required
Frequency*
Model*
Output
Frequency Stability (over operating temperature range)*
Operating Temperature Range*
Supply Voltage
- Example
26.0MHz IQXT-225-12
Clipped Sine $\pm 0.5\text{ppm}$ -30 to 85C 1.2V

Compliance

- RoHS Status (2011/65/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details

- Pack Style: Reel Tape & reel in accordance with EIA-481-D
Pack Size: 3,000
- Pack Style: Cutt Cut tape
Pack Size: 100

Electrical Specification - maximum limiting values 1.2V $\pm 5\%$

Frequency Min	Frequency Max	Temperature Range	Stability (Min)	Current Draw	Rise and Fall Time	Duty Cycle
		°C	ppm	mA	ns	%
16.368MHz	38.4MHz	-30 to 85	± 0.5	1.7	-	-

This document was correct at the time of printing; please contact your local sales office for the latest version.

[Click to view latest version on our website.](#)

Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: 0800 1808 443

France: 0800 901 383
USA: +1.760.318.2824

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IQD Frequency Products:](#)

[LFTCXO077226Cutt](#) [LFTCXO077231Reel](#) [LFTCXO077230Cutt](#) [LFTCXO077228Reel](#) [LFTCXO077227Cutt](#)
[LFTCXO077230Reel](#) [LFTCXO077231Cutt](#) [LFTCXO077226Reel](#) [LFTCXO077229Reel](#) [LFTCXO077228Cutt](#)
[LFTCXO077229Cutt](#) [LFTCXO077227Reel](#)