


VISHAY / DALE 0.1% 金属膜电阻器, 高精度, 超高稳定性

PTF 类型系列

- 特性:
- 极低电阻温度系数
 - 特低噪声和电压系数
 - 出色的高频特性
 - 可更换绕线轴
 - 专利环氧覆膜提供良好的潮湿保护

尺寸: in. (mm)



型号	A	B	C	D
PTF56	0.250±0.031 (3.81±0.51)	0.091±0.009 (2.31±0.23)	0.300 (7.62)	0.025 (0.64)
PTF65	0.375±0.062 (9.53±1.57)	0.145±0.016 (3.68±0.41)	0.475 (12.07)	0.025 (0.64)

订购 200 只及以上者, 请来电询价。


贸泽电子料号	Vishay料号	阻值	TCR (ppm/°C)	容差 ±%	单价			
					1	25	50	100
PTF56, 1/8 W @ 85°C - 限制元件电压最大值 300								
71-PTF5649R900BYBF	PTF5649R900BYBF	49.9	10	0.10	7.75	7.15	6.79	6.56
71-PTF5650R000BYBF	PTF5650R000BYBF	50	10	0.10	7.75	7.15	6.79	6.56
71-PTF56100R00BXBF	PTF56100R00BXBF	100	15	0.10	12.14	11.18	10.88	9.69
71-PTF56100R00BYBF	PTF56100R00BYBF	100	10	0.10	7.75	7.15	6.79	6.56
71-PTF56200R00AYBF	PTF56200R00AYBF	200	10	0.05	13.86	13.04	11.77	10.88
71-PTF56200R00BYBF	PTF56200R00BYBF	200	10	0.10	9.98	9.16	8.72	8.05
71-PTF56250R00BYBF	PTF56250R00BYBF	250	10	0.10	13.19	11.25	10.43	9.91
71-PTF56500R00BYBF	PTF56500R00BYBF	500	10	0.10	16.84	15.35	13.63	12.96
71-PTF561K0000BYBF	PTF561K0000BYBF	1K	10	0.10	12.67	11.62	11.40	10.13
71-PTF561K0000BZBF	PTF561K0000BZBF	1K	5	0.10	21.75	18.55	16.02	14.08
71-PTF562K0000BYBF	PTF562K0000BYBF	2K	10	0.10	9.16	8.34	7.45	7.06
71-PTF563K0000BYBF	PTF563K0000BYBF	3K	10	0.10	7.38	6.56	5.96	5.66
71-PTF563K8800BZBF	PTF563K8800BZBF	3.88K	5	0.10	14.60	13.34	11.85	11.25
71-PTF564K9900BYBF	PTF564K9900BYBF	4.99K	10	0.10	7.38	6.56	5.96	5.66

贸泽电子料号	Vishay料号	阻值	TCR (ppm/°C)	容差 ±%	单价			
					1	25	50	100
PTF56, 1/8 W @ 85°C - 限制元件电压最大值 300 (续)								
71-PTF565K0000BYBF	PTF565K0000BYBF	5K	10	0.10	7.38	6.56	5.96	5.66
71-PTF565K0000BZBF	PTF565K0000BZBF	5K	5	0.10	10.13	9.01	8.20	7.60
71-PTF567K5000BYBF	PTF567K5000BYBF	7.5K	10	0.10	7.38	6.56	5.96	5.66
71-PTF5610K000BXBF	PTF5610K000BXBF	10K	15	0.10	8.94	8.12	7.24	6.88
71-PTF5610K000BYBF	PTF5610K000BYBF	10K	10	0.10	10.73	7.45	6.56	5.96
71-PTF5610K000BZBF	PTF5610K000BZBF	10K	5	0.10	10.13	9.01	8.20	7.60
71-PTF5611K000BYBF	PTF5611K000BYBF	11K	10	0.10	9.16	8.34	7.45	7.06
71-PTF5615K000BYBF	PTF5615K000BYBF	15K	10	0.10	9.16	8.34	7.45	7.06
71-PTF5620K000BYBF	PTF5620K000BYBF	20K	10	0.10	10.73	7.45	6.56	5.96
71-PTF5620K000BZBF	PTF5620K000BZBF	20K	5	0.10	10.13	9.01	8.20	7.60
71-PTF5624K900BYBF	PTF5624K900BYBF	24.9K	10	0.10	9.16	8.34	7.45	7.06
71-PTF5650K000BZBF	PTF5650K000BZBF	50K	5	0.10	10.13	9.01	8.20	7.60
71-PTF56100K00BYBF	PTF56100K00BYBF	100K	10	0.10	7.38	6.56	5.96	5.66
71-PTF56100K00BZBF	PTF56100K00BZBF	100K	5	0.10	10.13	9.01	8.20	7.60
71-PTF56200K00BZBF	PTF56200K00BZBF	200K	5	0.10	11.62	11.40	11.18	11.03
71-PTF56249K00BYBF	PTF56249K00BYBF	249K	10	0.10	20.86	19.00	16.91	16.02
71-PTF56249K00BZBF	PTF56249K00BZBF	249K	5	0.10	31.36	26.15	24.81	20.64
71-PTF56300K00BZBF	PTF56300K00BZBF	300K	5	0.10	31.36	26.15	24.81	20.64
71-PTF56499K00BZBF	PTF56499K00BZBF	499K	5	0.10	31.36	26.15	24.81	20.64
PTF65, 1/4 W @ 85°C - 限制元件电压最大值 500								
71-PTF6550R000BYBF	PTF6550R000BYBF	50	10	0.10	12.44	11.70	10.95	10.28
71-PTF65100R00BYBF	PTF65100R00BYBF	100	10	0.10	16.09	14.68	13.04	12.37
71-PTF65120R00BYBF	PTF65120R00BYBF	120	10	0.10	12.44	11.70	10.95	10.28
71-PTF65250R00AYBF	PTF65250R00AYBF	250	10	0.05	13.41	11.47	9.91	9.46
71-PTF65400R00AZBF	PTF65400R00AZBF	400	5	0.05	23.06	26.45	23.54	22.35
71-PTF651K0000BYBF	PTF651K0000BYBF	1K	10	0.10	16.09	14.68	13.04	12.37
71-PTF6510K000BZBF	PTF6510K000BZBF	10K	5	0.10	16.39	14.90	13.26	12.59
71-PTF65100K00BYBF	PTF65100K00BYBF	100K	10	0.10	12.44	11.70	10.95	10.28
71-PTF651M0000BYBF	PTF651M0000BYBF	1M	10	0.10	11.25	10.28	9.09	8.64
71-PTF651M0000BXBF	PTF651M0000BXBF	1M	15	0.10	10.65	9.69	8.64	8.20

VISHAY / DALE 1% 金属膜电阻器 - 1/8, 1/4 和 1/2 W

RN 系列

- 特性:
- 特低噪声
 - 特低电压系数
 - 出色的高频特性
 - 符合 MIL-R-10509
 - 阻燃环氧涂层



尺寸: in.

系列号	A	B	C	D
RN55D	.240±.020	.090±.008	.278	.025±.002
RN60D	.344±.031	.145±.015	.425	.025±.002
RN65D	.562±.031	.180±.015	.687	.025±.002

RN55D, 1/8W

贸泽电子料号	阻值范围 (Ω)	单价				
		1	50	100	500	1000
71-RN55D-F-Value	10-1M	.67	.522	.462	.417	来电

RN60D, 1/4W

71-RN60D-F-Value	10-1M	3.13	2.53	2.16	1.89	来电
------------------	-------	------	------	------	------	----

RN65D, 1/2W

71-RN65D-F-Value	10-1.0M	2.31	1.86	1.49	1.34	来电
------------------	---------	------	------	------	------	----


如需其他参数的产品, 请致电 Mouser 销售代表或在 mouser.cn 网站上订购。

库存阻值表

RN55D-F 1/8 W						RN60D-F 1/4 W			RN65D-F 1/2 W		
10	221	825	4.32K	13.3K	200K	10	750	15K	10	5.62K	182K
15	243	909	4.75K	15K	249K	20	825	20K	100	6.81K	221K
20	249	1K	4.99K	18.2K	301K	24.9	1K	22.1K	200	10K	301K
22.1	267	1.21K	5.11K	20K	475K	49.9	1.1K	33.2K	221	15K	475K
27.4	274	1.5K	5.62K	22.1K	499K	75	1.21K	49.9K	332	20K	499K
33.2	301	1.82K	6.04K	27.4K	1M	100	1.5K	100K	475	22.1K	1M
47.5	332	2K	6.19K	30.1K	121	1.82K	150K	681	33.2K		
49.9	392	2.21K	6.81K	33.2K	150	2K	200K	825	39.2K		
56.2	402	2.37K	7.5K	47.5K	200	2.21K	221K	1K	47.5K		
75	432	2.49K	8.06K	49.9K	221	2.74K	499K	1.5K	49.9K		
90.9	475	2.74K	8.25K	51.1K	243	3.01K	1M	1.82K	56.2K		
100	499	3.01K	9.09K	75K	249	4.99K		2.21K	68.1K		
121	511	3.32K	10K	80.6K	301	5.62K		2.74K	100K		
150	562	3.65K	11K	82.5K	332	6.81K		3.32K	110K		
182	681	3.92K	12.1K	100K	475	10K		4.75K	121K		
200	750	4.02K	13K	150K	499	12.1K		4.99K	150K		

VISHAY / DALE 金属膜电阻器 - 1/4、1/2、3/4 和 1 W, ±1% 容差

CCF55, CCF60 系列



尺寸: IN

型号	A	B	C	D	E
CCF-55	.240±.020	.090±.008	.265	.025±.002	1.100±.040
CCF-60	.344±.031	.139±.009	.400	.025±.002	1.000±.040

特性:

- ±100PPM/°C 低温度系数
- 卓越的电气性能
- 阻燃环氧共形涂层
- 安装后易于辨认的标准5 段颜色代码印记
- 编带包装

规格:

- 额定功率: CCF55=1/4 & 1/2 W
CCF60=1/2、3/4 & 1 W
- 绝缘电阻: 10,000 MΩ
- 工作温度: -65°C 至 165°C

订购 10000 只及以上者, 请来电询价。

贸泽电子料号	阻值范围 (Ω)	单价			
		1	100	1000	5000
71-CCF55-Value	10-2.49M	-	-	-	-
71-CCF60-Value	10-1M	.75	.522	.447	.373

库存阻值表

10	75	340	866	2.49K	7.15K	18.2K	71.5K	267K
15	82.5	392	1K	2.74K	7.5K	20K	75K	274K
16.2	100	402	1.07K	2.8K	7.68K	22.1K	82.5K	301K
20	105	422	1.1K	3.16K	8.25K	27.4K	90.9K	332K
22.1	120	432	1.21K	3.32K	8.45K	30.1K	100K	392K
24.9	121	475	1.3K	4.32K	8.87K	33.2K	110K	475K
27.4	150	499	1.33K	4.53K	10K	39.2K	121K	499K
30.1	200	510	1.5K	4.75K	10.2K	40.2K	133K	1M
39.2	220	562	1.62K	4.99K	11K	47.5K	137K	1.5M
47.5	221	604	1.82K	5.11K	12.1K	49.9K	150K	2M
49.9	243	619	2K	5.62K	13K	51.1K	162K	2.21M
51.1	249	681	2.15K	6.04K	14K	56.2K	200K	2.49M
60.4	301	750	2.21K	6.19K	15K	68.1K	221K	
73.2	332	825	2.43K	6.81K	16.2K	68.1K	249K	

FRJ-50 型零欧姆跳线电阻器

- 特性:
- 提供低电阻电路互联
 - 阻燃涂层
 - 与自动插入设备相容

规格:

- 电阻: 0.01Ω 最大值
- 绝缘电阻: 干 10,000MΩ; 湿 100MΩ
- 引线材料: 镀锡铜 (最大 98% 锡)

尺寸: in. (mm)

