








SYMBOL DEFINITION		MISSING NUMBERS	
THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	19	
	LAST NO. USED	28	

DATE		DRG STATUS	REV	N/P	CHG	ZONE	REVISION HISTORY		AUTH	DR	APVD	APVD
15DE98	R	01	-	-	-	-	WAS PE072106 AND RELEASED		990005	SAW	SAW	RB
03MY99	R	02	-	-	-	-	REVISED		193395	DRR	DRR	RB
03MY99	R	03	-	-	-	-	REVISED WALL THICKNESS		193917	DRR	DRR	RB
03AU99	R	04	-	-	-	-	REVISED INDEXING RIBS		194115	BD	BD	RB
050C99	R	04	AA	-	-	-	RELAXED TOLERANCES		195604	LMB	LMB	RB
070C99	R	05	-	-	-	-	REVISED MATERIAL SAVER		195629	JR	JR	RB
18FE02	R	05	AA	-	-	-	REMOVED RIBS (2 PLCS) AND RELAXED TOLERANCES		221179	TMP	TMP	RAB
190C05	R	05	AB	-	-	-	UPDATED PDM ATTRIBUTES		273735	EAF	EAF	EM



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA. ALL RADII 0.40 DRAFT IS 1° ON ALL OUTSIDE SURFACES LIKE CAVITIES ARE IDENTICAL LOCKING FEATURES ARE IDENTICAL
- MATING COMPONENTS OR EQUIVALENT:
TERMINAL 12065915
INSERT NUT 15319432
SECONDARY TERMINAL LOCK 15329013 (2 REQUIRED)
LOWER HOUSING 15329043
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
MAX. INSULATION CRIMP MUST BE LESS THAN 5.2 HIGH AND 8.0 WIDE
MAX CABLE O.D. 4.6
- THIS PART IS USED IN ASSEMBLY 15328970 OR EQUIVALENT.



DRG TYPE		PART DRAWING	
STYLE			
VOLUME (CM) 42.467		DISTR CODE D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.			

UNLESS OTHERWISE SPECIFIED
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994
AS AMENDED BY THE 2018 ADDENDUM TO Y14.5M-1994
TOLERANCING ADDENDUM-2018. SEPARATE PATTERNING OF
FEATURES MAY BE GIVEN SEPARATELY REGARDLESS OF DATUM
REFERENCES.

ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	001, 701

(N/A) PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE UNITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART E
FROM 0 TO 20	> 30 > 70 > 100
TO 20 30 70 100	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.15 ±0.2 ±0.3 ±0.4 ±0.5	
ANGULAR TOLERANCE 12°	

THIRD ANGLE PROJECTION	
DO NOT SCALE	USE MATH DATA



DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR R. HARTMAN	DATE 21 JUL 98
APVD1 B. DAGGETT	03AU99
APVD2 B. DAGGETT	03AU99
APVD3 R. BALDWIN	09AU99
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL R0071754 PA66 HS 1M-BLK	
DRAWING NAME CONN 8 F M/P 800 BLK	
DRAWING NUMBER 15329011	
SIZE A0	SCALE 2:1
FRAME NO 1	SHEET NO 1 OF 1
REV R	DATE 05 AB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[15329011](#)