












PROTECTION OR / GOLD PLATING						
		Pitch of the strip = 15.20 65 terminals per meter				
Reference	Area	Ni B	C	Sn (μm)	Thickness Au nominal / mini	
211 CC 2S X 4 60	B2 (INT)	1 μMIN 2 μMAX	0.1 μMAX		1.52 μ	1.27 μ
211 CC 2S X 4 61	Contact point					

ZONE ET DIMENSIONS VARIABLES POUR TOUTES REFERENCES
AREA AND DIMENSIONS ARE VALID FOR ALL REFERENCES



✓ PAS DE TROU POUR SECTION 0.22
NO HOLE FOR GAUGE 0.22

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[211CC2S1190P-L](#) [211CC2S2150-L](#) [211CC2S4161P-L](#)