

DC Pass Bi-Directional Coupler

50Ω Up to 100W 800 to 2500 MHz

ZABDC20-252H-S+

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	2.0 A

* Case temperature is defined as temperature on ground leads.
Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

INPUT	1
OUTPUT	4
COUPLED (forward)	2
COUPLED (reverse)	3

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	
2.00	2.00	.88	.90	.156	1.688	.125	
50.80	50.80	22.35	22.86	3.96	42.88	3.18	
H	J	K	L	M		wt	
.38	---	.50	1.00	1.25		grams	
9.65	---	12.70	25.40	31.75		225	

Features

- excellent mainline loss, 0.17 dB typ.
- excellent directivity, 28 dB typ.
- high power, up to 100W
- rugged shielded case
- DC current through input to output 2.0A Max. at 50 watt RF input power

Applications

- PCS/DCS/UMTS
- power leveling & monitoring
- VSWR measurement



SMA version shown
CASE STYLE: DD477-1

Connectors	Model
SMA	ZABDC20-252H-S+
N-TYPE	ZABDC20-252H-N+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Bi-Directional Coupler Electrical Specifications

FREQ. (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)		DIRECTIVITY (dB)		VSWR (:1)	POWER INPUT (W)
f_L - f_U	Norm.	Flatness	Typ.	Max.	Typ.	Min.	Typ.	Max.
800-2500			0.20	0.35	28	20	1.05	50
800-1000	23±1.0	±0.9	0.15	0.25	30	23	1.05	100
1300-2500	19.7±0.7	±0.75	0.20	0.35	28	20	1.05	50


1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB)		Coupling (dB)		Directivity (dB)		Return Loss (dB)			
	In-Out	In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd	Cpl Rev	
800.00	0.11	23.88	23.85	32.78	36.66	39.78	35.40	47.06	42.20	
1000.00	0.12	22.32	22.28	30.17	32.23	39.27	35.77	38.27	37.38	
1200.00	0.13	21.22	21.15	31.42	32.87	35.59	36.09	34.59	34.96	
1400.00	0.15	20.43	20.38	35.46	36.13	32.74	34.79	33.78	35.02	
1600.00	0.17	19.92	19.86	42.35	35.55	30.21	33.34	31.94	33.00	
1800.00	0.19	19.63	19.58	32.79	29.28	29.43	33.84	33.22	32.26	
2000.00	0.20	19.58	19.54	28.91	26.99	30.64	33.90	36.72	35.98	
2200.00	0.21	19.77	19.73	28.11	26.09	31.14	35.70	41.69	36.37	
2400.00	0.21	20.21	20.16	27.14	25.13	35.33	36.16	49.29	35.25	
2500.00	0.21	20.53	20.48	27.45	24.97	37.60	37.56	38.44	34.58	



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR BI-DIRECTIONAL COUPLER WITHOUT INTERNAL TRANSFORMERS AND RESISTORS.

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
M171494
ED-11579/4
ZABDC20-252H-S+
WP/QL/AM
181226
Page 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[ZABDC20-252H-S+](#)