

Coaxial Directional Coupler

50Ω

20 to 2000 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

Coaxial Connections

INPUT	3
OUTPUT	1
COUPLED	2


Outline Drawing






Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
1.25	1.25	.75	.63	.38	1.00	.125	1.000
31.75	31.75	19.05	16.00	9.65	25.40	3.18	25.40
J	K	L	M	N	P	Q	wt
--	--	.125	1.688	2.18	.75	.07	grams
--	--	3.18	42.88	55.37	19.05	1.78	70.0

Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

ZFDC-6-23-S+



Generic photo used for illustration purposes only

CASE STYLE: K18

Connectors	Model
SMA	ZFDC-6-23-S+
BRACKET (OPTION "B")	

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Features

- very wideband, 20 to 2000 MHz
- good directivity, 17 dB typ.
- can be used for unbalance 2 way splitter
- rugged shielded case

Applications

- cellular
- instrumentation
- communication receivers & transmitters
- GPS

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		20		2000	MHz
Mainline Loss ¹	20-1300	—	2.0	2.8	dB
	1300-2000	—	2.7	3.5	dB
Nominal Coupling	20-2000	—	6.4±0.5	—	dB
Coupling Flatness(±)	20-2000	—	0.3	0.7	dB
Directivity	20-2000	11	18	—	dB
Return Loss (Input)	20-700	11	16	—	dB
	700-1600	15	22	—	dB
	1600-2000	12	18	—	dB
Return Loss (Output)	20-700	14	22	—	dB
	700-1600	17	24	—	dB
	1600-2000	14	22	—	dB
Return Loss (Coupling)	20-700	11	16	—	dB
	700-1600	10	15	—	dB
	1600-2000	10	14	—	dB
Input Power	20-2000			0.5	W

1. Include coupling loss.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	In	Return Loss (dB) Out	Cpl
20	2.13	6.64	15.21	13.94	17.62	13.81
50	1.94	6.58	15.87	15.69	22.88	15.49
200	1.86	6.59	16.01	17.46	26.12	16.89
400	1.89	6.58	15.95	18.53	26.28	17.24
700	1.94	6.50	15.95	20.19	25.13	17.28
1000	2.04	6.39	16.12	22.58	23.61	16.88
1300	2.22	6.28	16.52	25.66	22.97	15.80
1600	2.48	6.18	16.54	25.36	21.71	14.31
1800	2.72	6.14	15.80	22.29	20.07	13.41
2000	3.02	6.12	14.54	18.96	17.99	12.50

REV. OR
ECO-001941
ZFDC-6-23-S+
ED-19081401
YL/CP/AM
200226

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mini-Circuits:](#)

[ZFDC-6-23B-S+](#)