


CODE 1

PART-NO.: 15498443

COLOR BLK

SCALE:

2:1




CODE 2

PART-NO.: 13891366

COLOR GRA

SCALE:

2:1




CODE 3

PART-NO.: 15498444

COLOR NAT


SCALE:

2:1



TOOL CAVITY NUMBER / FORMAT
ACCORDING TO DIN 1451: 1.6 MM HIGH

INDEX REPLACEMENT INSERT /
FORMAT ACCORDING TO DIN 1451: 1.6 MM HIGH




REMARKS:

MATING PART: RECEPTACLE HOUSING 2 WAY DWG-NO.: 15426724

ADDITIONAL ACCESSORIES: CLIP DELPHI DRAWING-NO.: 15439876
CLIP DELPHI DRAWING-NO.: 15432535



LETTERS AND ENGRAVINGS 0.2 MM RAISED

COD	TITLE	PART-NO.:	AMOUNT	CABEL RANGE	SEAL PART-NO.:	MATERIAL	NOTES
-	MALE TERMINAL 2.8	2-964298-1	2	0.35-1 MM ² FLRY	15327860	CUFE2P BLU	NOT SHOWN ON DRAWING
		2-964300-1	2	1.5-2.0 MM ² FLRY	15327863	CUFE2P RED/BRN	NOT SHOWN ON DRAWING
		2-964302-1	2	2.5 MM ² FLRY	15327859	CUFE2P YEL	NOT SHOWN ON DRAWING



MATERIAL NAME ACCORDING TO VDA 260 /
FORMAT ACCORDING TO DIN 1451: 1.2 MM HIGH
0.05 MM RAISED


MANUFACTURER MARK A=1.2 MM 0.05 MM RAISED
FORMAT ACCORDING TO DS 11001



COD	TITLE	PART-NO.:	PART- REV	DATE	AMOUNT	MATERIAL	SIMILAR TO RAL
1	TAB HOUSING 2 WAY	15498443	01	09JL04	1	PA6.6 6F30 BLK	9005
2	TAB HOUSING 2 WAY	13891366	01	16JN11	1	PA6.6 6F30 GRA	7001
3	TAB HOUSING 2 WAY	15498444	01	09JL04	1	PA6.6 6F30 NAT	---

DATE INSERT SIMILAR FIRM HASCO Z 485/4/1:
HAS TO BE THE MANUFACTURING DATE

SEALING SURFACES MUST BE FREE OF DEFECTS, PARTING
LINES, MOLD MISMATCH AND KNIT LINES FOR SEALING.
SURFACE MUST BE POLISHED IN DEMOLDING DIRECTION.




DIMENSIONAL RANGE (MM)	CHART E.1									
	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300
TO	0	20	30	70	100	150	200	250	300	400
TOLERANCE UNLESS OTHERWISE SPECIFIED										
	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	
ANGULAR TOLERANCE ±2°										

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	1	
DATE	STG	REV	N	P/CHG					APVD 1	APVD 2
18JN14	R	01				INITIAL RELEASE			K.JAN	M.SKR

SCALE:

1:1



DWG TYP
PART DRAWING

WEIGHT (GR)
4.1

VOLUME (CM³)
3.0

ROUTING

DISTR CODE
D

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE CHART

GD&T
ACCORDING TO:
ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

DELPHI

DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE

KRAKOW, POLAND

COPYRIGHT 2014 DELPHI CORPORATION AND/OR ITS AFFILIATES.
ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION
AND CONTAINS DELPHI CONFIDENTIAL INFORMATION.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION
OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA,
AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS,
WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WŁASNOŚCIĄ DELPHI CORPORATION I ZAWIERA POŁPNE
INFORMACJE. POWIELANIE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO
DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZESYŁANIE
INNYM JAKIEKOLWIEKICH ZAWARTOŚCI, BEZ NADANIA WYRAZNYCH
UPRAWIEŃ, JEST ZABRONIONE

DR	K.JANKOWSKI	DATE	18JN14
APVD1	M.SIKORA		18JN14
APVD2	M.SIKORA		18JN14
APVD3			
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKREŚLA
DELPHI 10949001

MATERIAL
SEE CHART

DRAWING NAME
TAB HOUSING 2 WAY
FOR TERMINAL 2.8 X 0.8

DRAWING NUMBER
15498442

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	5:1	1 OF 1	1 OF 1	R	01	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15498443](#)