




SYMBOL DEFINITION			MISSING NUMBERS
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	10	
	LAST NO. USED	10	

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
02AU99	R	001	-	--		CLEARED REV COLUMN & REVISED PACKAGING DETAILS	195707	CRW	JHV	RJ
04FE00	R	002	-	-		UPDATED PDM ATTRIBUTES	198936	JTV	JVM	RJ
04FE00	R	003	-	-		15359001 & 15359002 - RELEASED	000005	JTV	JVM	RJ
26AP00	R	004	-	-		UPDATED PDM ATTRIBUTES	200791	WRC	WRC	RJ
08AU00	R	005	-	-		REVISED ALL PARTS - ADDED NOTE #3	202594	JHH	JHH	DJ
22MR05	R	06	-	-		15359001 - UPDATED PDM ATTRIBUTES ALL PARTS - ADDED CONN & PIN IN CHART, ADDED NOTE #4, REVISED NOTE #2	266170	TAI	TAI	A6L
07DE05	R	07	-	-		15359001 - UPDATED PDM ATTRIBUTES	275453	DAD	DAD	CJF



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:


DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. REFERENCE MATING COMPONENTS OR EQUIVALENT: SEE CHART

3. TERMINAL MUST FIT A MAX. Ø2.54 MM GAGE HOLE 12 MM DEEP AFTER CRIMPING.

4. "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE DIE SERIES NUMBER (PO1, PO2, PO3, ETC).

15359002	001	AB		0.2 X 36.5	M3696FN3 METL NONFERROUS C42500 1/2 HD	0.8	18	2.04 ±0.08	2.5 ±0.2	3.2 ±0.2	0.5	0.7	0.5	12129025	12092396
15359001	001	AD		0.2 X 36.5	M3696FN3 METL NONFERROUS C42500 1/2 HD	0.35 - 0.5	21	1.92 ±0.08	2.1 ±0.2	3.2 ±0.2	0.5	0.7	0.5	12129025	12092396
12176829	E6			0.2 X 36.5	M3661CNI METL NONFERROUS C42500 1/2 HD	0.8	18	2.04 ±0.08	2.5 ±0.2	3.2 ±0.2	0.5	0.7	0.5	12129025	12092396
12176828	E6			0.2 X 36.5	M3661CNI METL NONFERROUS C42500 1/2 HD	0.35 -0.5	21	1.92 ±0.08	2.1 ±0.2	3.2 ±0.2	0.5	0.7	0.5	12129025	12092396
PART NO	REV	N/P	STATUS	MAT'L SIZE	MAT'L SPEC	SIZE (MM²)	ID	DIA	D	E	F±0.2	G±0.2	H±0.2	CONN	PIN

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM³)	DISTR CODE		
	D		
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION	DO NOT SCALE		
	USE MATH DATA		

DIMENSIONAL RANGE (MM)		CHART D
FROM	TO	
0	12	>12
TOLERANCE UNLESS OTHERWISE SPECIFIED		
±0.1		±0.2
ANGULAR TOLERANCE ±2°		

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
APVD1 CLAUDIA WYLER	06AU99
APVD2 JOSE HUERTA	06AU99
APVD3 JOSE HUERTA	06AU99
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE CHART	
DRAWING NAME TAXI TERM F MIC/P 100W NONE	
DRAWING NUMBER 12176830	
SIZE A1	SCALE 10:1
FRAME NO 1 OF 1	SHEET NO 1 OF 1
STG R	REV 07
N/P -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15359002-L](#)