




SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL □ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	18
	LAST NO. USED	15


MISSING SYMBOLS
NO MISSING SYMBOL NUMBER

DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG					
10SE03	R	01	-	-		CREATED PART DRAWING	245864	LMB	LMB SCH
240C03	R	02	-	-		UPDATED REVISION LEVEL IN CHART.	247535	LMB	LMB RF
26JN07	R	03	-	-		ADDED PN 15369015, REVISED SHEET NO, REVISED MAT'L WAS PM003659-A23, ADDED APPLICATION COLUMN, REMOVED COLUMN "LOWER CONTACT TYPE" AND "REF P/N EPEC", REVISED "TYPE" LABEL WAS TYPE 1 AND 2, REVISED INSPECT SYMBOL	401146	ETG	CMO ASG
16JN10	R	04	-	-		ADDED PN 13793741	409252	CPD	SCS ASG
24FE12	R	05	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES	417234	JCF	JVM OAF




INSULATION WINGS FOR
(SEE CHART) MAX INSULATION DIA


CONDUCTOR WINGS FOR
(SEE CHART) MM² CABLE




TYPE 201



TYPE 202



3 RIB SEAL POSITION REF
SCALE 5:1



2 RIB SEAL POSITION REF
AND TERMINAL & CABLE ALIGNMENT
SCALE 5:1

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATING COMPONENTS OR EQUIVALENT:
TERMINAL 15304704
- * DENOTES DIMENSIONS MADE AT CUT-OFF AND CRIMP DIE.

13793741	01	AA	-	0.3 X 27.38	SN PLATED COPPER ALLOY	1 - 1.5	16	2.4 - 1.9	SEALED (MINI)	201	2.95
15369015	12	AA	-	0.3 X 27.38	AU PLATED COPPER ALLOY	0.75 - 1	17	2.1 - 1.7	SEALED (MINI)	201	2.65
15396680	02	AB	-	0.3 X 27.38	SN PLATED COPPER ALLOY	0.35 - 0.5	21	1.85 - 1.2	SEALED (MINI)	202	2.1
15396679	02	AB	-	0.3 X 27.38	SN PLATED COPPER ALLOY	0.75 - 1	17	2.1 - 1.7	SEALED (MINI)	202	2.65
15396678	02	AB	-	0.3 X 27.38	SN PLATED COPPER ALLOY	0.5 - 1	17	2.1 - 1.4	SEALED (150MP)	201	2.65
15396677	02	AB	-	0.3 X 27.38	SN PLATED COPPER ALLOY	1 - 1.5	16	2.4 - 1.9	SEALED (150MP)	201	2.95
15396676	02	AB	-	0.3 X 27.38	SN PLATED COPPER ALLOY	1.5 - 2.5	14	3 - 2.2	SEALED (150MP)	201	3.75
PART NO	REV	N/P	STATUS	MAT'L SIZE	MAT'L SPEC	SIZE (MM ²)	ID	DIA	MAT'L SPEC	TYPE	DIA

(10) PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART D
FROM 0	>12
TO +12	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.1	±0.2
ANGULAR TOLERANCE ±2°	

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM ³)		DISTR CODE	
		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE. ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
		USE MATH DATA	
			

DELPHI			
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH			
DR L.M. BASKIN			DATE 10SE03
APVD1 L.M. BASKIN			10SE03
APVD2 L.M. BASKIN			10SE03
APVD3 E. HSIEH			10SE03
APVD4			
APVD5			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001			
MATERIAL SEE CHART			
DRAWING NAME TAXI TERM F GT 150 SEALED			
DRAWING NUMBER 15305538			
SIZE A1	SCALE 10:1	FRAME NO 1 OF 1	SHEET NO 2 OF 2
STG R	REV 05	N/P -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15396679](#) [15396677](#) [15396680](#) [15396678](#)