

MEF EMC-FILTER 3-PHASE 1-STAGE

I:80A U:3x600 VAC book-style

Art.No.: 10537

Weight: 2.2

Country of origin: IT



Model designation: MEF 3/1 80A T

Current: 80 A

1-stage

Attenuation curves on request.

The MEF 3/1-3/2 3-phase and 1-/2-stage mains suppression filters are used in the 0.1...30 MHz range to suppress conducted interference on mains and supply lines. They are suitable for TN-C networks. The best filter effect is achieved with short connecting lines (recommendation: PE connection < 10 cm) with the largest possible cross sections. Line suppression filters act bidirectionally (in both directions). They reduce symmetrical and asymmetrical interference, which often occurs with frequency converters and switched-mode power supplies.

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

The information in this Product-PDF has been compiled with the utmost care.
 Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-08-16

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Material short text	MEF 3/1 80A T
Commercial data	
URL Webshop	https://shop.murrelektronik.com/10537
GTIN	4048879029209
ECLASS-6.0	27130806
ECLASS-6.1	27420201
ECLASS-7.0	27420290
ECLASS-7.1	27420290
ECLASS-8.0	27420290
ECLASS-8.1	27420290
ECLASS-9.0	27420208
ECLASS-9.1	27420290
ECLASS-10.0.1	27420290
ECLASS-10.1	27420208
ECLASS-11.0	27420290
ECLASS-11.1	27420208
ECLASS-12.0	27420208
ECLASS-13.0	27420290
ECLASS-14.0	27420290
ETIM-5.0	EC002498
ETIM-6.0	EC002498
ETIM-7.0	EC002498
ETIM-8.0	EC002498
customs tariff number	85363030
EAN	4048879029209
Packaging unit	1
Electrical data	
Leakage current max.	10 mA @ 250 V AC, 50 Hz
Electrical data Supply	
Power frequency	50 ... 60 Hz
Operating voltage AC max.	600 V
Electrical data Input	
Phase number input	3
Electrical data Output	
Overload current	18× (IN t) max. 0.5 ms; 1.5× (IN t) max. 1 min. (1× per hour)
Installation	
Connection cross-section solid min.	6 mm ²
Connection cross-section solid max.	35 mm ²
Connection cross-section stranded/fine-stranded min.	10 mm ²
Connection cross-section stranded/fine-stranded max.	35 mm ²
AWG number solid min.	9
AWG number solid max.	2
AWG number stranded/fine stranded min.	7
AWG number stranded/fine stranded max.	2
Device protection Electrical	
Insulation test voltage L-N	33 kV
Insulation test voltage L-L	31 kV
Duration insulation test voltage	2 s
Mechanical data Mounting data	

Height	270 mm
Width	90 mm
Depth	150 mm
Mounting method	screwed

Environmental characteristics | Climatic

Climatic category (EN IEC 60068-1)	25/085/21
------------------------------------	-----------

Connection type 2

Family construction form	terminal
No. of poles	3
Gender	female
Color contact carrier	gray
Connection	Screw terminals SK
PIN 1	L 1
PIN 2	L 2
PIN 3	L 3
Family construction form	terminal
No. of poles	3
Gender	female
Color contact carrier	gray
Connection	Screw terminals SK
PIN 1	L 1'
PIN 2	L 2'
PIN 3	L 3'

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[10537](#)