

CUBE67 I/O COMPACT MODULE

4 analog inputs (I)
Art.No.: 56730
Weight: 0.14
Country of origin: DE
Model designation: Cube67 AI4 C 4xM12 (I)


Compact module
AI4 - (C) 4x M12 (I)
Current
Connection cables are in the online shop under "Connection Technology".
Housing fully potted.

Link to Product

Illustration



Product may differ from Image



Header	
Material short text	Cube67 AI4 C 4xM12 (I)
Commercial data	
URL Webshop	https://shop.murrelektronik.com/56730
GTIN	4048879048224
ECLASS-6.0	27242601
ECLASS-6.1	27242601
ECLASS-7.0	27242601
ECLASS-7.1	27242601
ECLASS-8.0	27242601
ECLASS-8.1	27242601
ECLASS-9.0	27242601
ECLASS-9.1	27242601
ECLASS-10.0.1	27242601
ECLASS-10.1	27242601
ECLASS-11.0	27242601
ECLASS-11.1	27242601

ECLASS-12.0	27242601
ECLASS-13.0	27242601
ECLASS-14.0	27242601
ETIM-5.0	EC001596
ETIM-6.0	EC001596
ETIM-7.0	EC001596
ETIM-8.0	EC001596
customs tariff number	85389099
EAN	4048879048224
Packaging unit	1

Electrical data | Supply

Norm operating voltage	EN 61131-2
Operating voltage US DC	24 V
Total current US max.	4 A
Total current UA max.	4 A
Current consumption max.	50 mA

Electrical data | Input

Input current min.	0 mA
Input current max.	20 mA
Current input mode 2 min.	4 mA
Current input mode 2 max.	20 mA
Sensor current US per input max.	0.2 A
Short-circuit protected	yes
Overload resistant	yes
Differential input	yes
Working resistance max.	300 Ω
Conversion time analog input per channel	2 ms

Diagnostics

Actuator warning	per channel via LED and BUS
Short circuit diagnosis	yes
Overload diagnosis	yes
Diagnostic	No voltage, Under voltage
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module and channel
LED display	Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
-------------------------------------	------

Mechanical data | Mounting data

Height	126 mm
Width	30 mm
Depth	34.5 mm
Suitable for mounting type	2-hole screw mounting

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-20 °C
Storage temperature max.	75 °C

Connection type 2

Connection type 1	0-3
Connection type 2	Bus In
Family construction form	M12

No. of poles	5
Coding	A
Gender	female
Color contact carrier	black
PIN 1	24 V DC (US)
PIN 2	AI +
PIN 3	0 V
PIN 4	AI -
PIN 5	n.c.
Family construction form	M12
No. of poles	6
Coding	A
Gender	male
Color contact carrier	black
PIN 1	24 V DC (UA)
PIN 2	24 V DC (US)
PIN 3	0 V
PIN 4	Bus internal
PIN 5	Bus internal
PIN 6	0 V

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrelektronik:](#)

[56730](#)