

## EFD Cores (8995202021)



Part Number: 8995202021

95 EFD CORE CORE

EFD (Economical Flat Design) cores have been designed to maximize volume in a low profile geometry. EFD cores allow maximum throughput power density with reasonably low mass for board level installation.

EFD cores can be supplied with the center post gapped to a mechanical dimension or an A<sub>t</sub> value.

## Catalog Drawing 3D Model

Weight indicated is per pair or set.

Weight: 7 (g)

WCISII	<u>u.</u> / (5)				
Dim	mm	mm tol	nominal inch	inch misc.	
A	20	± 0.55	0.787		-B
В	10	± 0.25	0.394		
С	6.65	± 0.20	0.262		
D	7.7	± 0.25	0.303		A L FE
Е	15.4	± 0.50	0.606		
F	8.9	± 0.30	0.35		, D, K,
K	3.6	± 0.15	0.142		* + ***

## **Chart Legend**

 $\Sigma I/A$ : Core Constant,  $I_e$ : Effective Path Length,  $A_e$ : Effective Cross-Sectional Area,  $V_e$ :

Effective Core Volume
A<sub>1</sub>: Inductance Factor

Explanation of Part Numbers: Digits 1 & 2 = product class and 3 & 4 = material grade.

Electrical Properties		
$A_L(nH)$	1400 ±25%	
Ae(cm <sup>2</sup> )	0.31	
$\Sigma l/A(cm^{-1})$	15.6	
l <sub>e</sub> (cm)	4.74	
$V_e(cm^3)$	1.44	
$A_{min}(cm^2)$	0.29	

 $A_L$  value is measured at 1 kHz, B < 10 gauss.

888-324-7748

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fair-Rite: 8995202021