


1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. CONTACT RATING: 50mA @12V DC
- ▲4. CONTACT MATERIAL: SILVER
- ▲5. OPERATING FORCE: 160±50gf
6. TRAVEL: 0.25 +0.2/-0.1
7. CONTACT RESISTANCE: 100mILLI Ohms max.
8. ELECTRICAL LIFE: 100,000 CYCLES
9. PACKAGING:
CARRIER IS FOLDED EVERY 25 PITCHES
(24) SWITCHES PER FOLD
(1,000) SWITCHES PER BOX
10. 2002/95/EC (ROHS) COMPLIANT
11. ▲DENOTES MAJOR DIMENSION.



RECOMMENDED P.C.B. LAYOUT

				
TITLE				
TL59CF160Q				
SCALE	DATE	DR	DWG	REV
2:1	1/19/2007	TN	P010581	B

B	16892	UPDATE NOTES, .30 TO .25	1/19/07	TN
A	11623	RELEASED FOR PRODUCTION	8/21/01	CB
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL59CF160Q](#)