


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
00	NEW RELEASE	18.08.20	QG


Cable Length	Part Number
1.0m(+0.05m/-0m)	FO-10GGBLCX20-001
2.0m(+0.10m/-0m)	FO-10GGBLCX20-002
3.0m(+0.10m/-0m)	FO-10GGBLCX20-003
4.0m(+0.10m/-0m)	FO-10GGBLCX20-004
5.0m(+0.10m/-0m)	FO-10GGBLCX20-005
6.0m(+0.10m/-0m)	FO-10GGBLCX20-006
10.0m(+0.10m/-0m)	FO-10GGBLCX20-010
15.0m(+0.10m/-0m)	FO-10GGBLCX20-015

B

B



LC CONNECTOR SET



A

A

N0	PART NAME
1	DUST CAP
2	PLUG HOUSING(BEIGE)
3	BARREL/FERRULE
4	SPRING
5	EXTENDER CAP(BEIGE)
6	CRIMP SLEEVE
7	CLIP(BEIGE)
8	BOOT (WHITE)

Specification

1. Marking: Amphenol Cables on Demand 10 GIGABIT OPTICAL FIBER CABLE LSZH xx/xx xxxxM
2. Fiber: Multimode 50/125um OM3 Optical Fiber
3. Fiber cord: 2.0*4.2mm ,LSZH Color Aqua
4. Operating wavelength: 850nm
5. Insertion Loss: $\leq 0.3\text{dB}$



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand		
				20 VALLEY ST. ENDICOTT, NY 13760		
DECIMALS .X .XX .XXX	ANGLES ii X ii XX ii XXX	APPROVALS	DATE	2.0*4.2mm Aqua LSZH LC-LC OM3 Patchcord		
		Lojing	20AUG2018			
		CHECKED	20AUG2018			
		Qingguo				
THIRD ANGLE PROJECTION 		RESP ENG		SIZE DWG. NO. REV. A FO-10GGBLCX20-XXX 00		
		MFG ENG				
CAD FILE:				SCALE	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[FO-10GGBLCX20-001](#) [FO-10GGBLCX20-002](#) [FO-10GGBLCX20-005](#) [FO-10GGBLCX20-010](#) [FO-10GGBLCX20-015](#)