

(Längen der Steck- und Anschlußseite gelten für eingepreßte Steckverbinder)
(mating and termination length of contacts apply to pressed in connectors)

K I M

N P Q

R S T

R S T

Referenzebene Tiefe
datum plane depth

Ebene 3 / level 3 : 11,2 ^{+0,2}
 Ebene 2 / level 2 : 9,7 ^{+0,2}
 Ebene 1 / level 1 : 8,2 ^{+0,2}

Steckbereich:
 length for mating:

3,7 $\pm$ 0,2
 13 $\pm$ 0,2
 min. 6
 14,5 $\pm$ 0,2
 min. 7,5
 16 $\pm$ 0,2
 min. 9

Referenzebene
 datum plane

Technical drawing of a rectangular plate. The drawing shows a grid of 21 columns and 4 rows of holes. The dimensions are as follows:

- Overall width: $44_{-0,1}$
- Overall height: $15,4 \pm 0,05$
- Distance between hole centers (pitch): 2
- Number of columns: $21 \times 2 (=42)$
- Number of rows: 4

Labels on the left side indicate the rows (Reihe / row) and columns (Spalte / column):

- Reihe / row: f, e, d, c, b, a, z
- Spalte / column: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21

Technical drawing of a rectangular plate with a grid of holes. The grid consists of 21 columns and 6 rows of holes. The holes are spaced at 2 units horizontally and 2 units vertically. The total width is 42 units (21 x 2) and the total height is 12 units (6 x 2). The drawing includes labels for 'Position' (1 to 22) and 'Reihe' (row) (a to f). A detail view shows a hole with a diameter of $\phi 0,6$ and a positional tolerance of $\phi 0,05$. The text 'all notes' is also present.



Empfohlener Lochaufbau und
weitere Informationen siehe: DS 17 00 110 0101
recommended configuration of plated through holes
and further information see: DS 17 00 110 0101

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances IEC 61076-4-101		
				Dat.	Name	Maßstab/Scale 2 : 1	har-bus HM Messerleiste Typ B-22 154pol., Anschlußlänge 3,7mm und 16mm har-bus HM male connector type B-22 154pol., termination length 3,7mm and 16mm				
			Detail.	17.12.99	HL.						
35965	05.01.10	Hage.	Insp.	17.12.99	Pa.						
34337	13.06.07	Hage.	Stand.								
28996	28.03.01	HL.	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP				TB 17 04 154 x010			Blatt/ page /	
26988											
Mod.	Dat.	Name				Sub.					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[17041541010](#) [17041542010](#)