


LTR	DESCRIPTION	DATE	BY
-	Released	6/14/99	JCL



I. MATERIALS & FINISHES

center contact: Gold Plated Beryllium Copper – female pin
 outer contact: Alballoy Plated Brass
 body: Alballoy Plated Brass
 coupling nut: Alballoy Plated Brass
 crimp sleeve: Alballoy Plated Copper
 dielectric: Teflon® PTFE
 gasket: Silicone Rubber
 shrink sleeve: Adhesive Lined Polyolefin
 crimp size: .429" hex (M22520/5-61)

II. ELECTRICAL PROPERTIES

impedance: 50 ohms
 working voltage: 500 vrms (max)
 vswr: 1.25:1 (max) up to 3 GHz
 insertion loss: $0.1 \times \sqrt{f_{\text{GHz}}}$

Unless otherwise specified, dimensions are in inches. Tolerances are applicable when specified.

These drawings and specifications contain proprietary information which is the property of Times Microwave Systems.

Approvals

Drawn	JCL	6/14/99
-------	-----	---------

Check		
-------	--	--

Prj. Mgr.		
-----------	--	--

Prd. Mgr.		
-----------	--	--

QA Mgr.		
---------	--	--



TIMES MICROWAVE SYSTEMS

Wallingford, CT 06492
 (203) 949-8400; (203) 949-8423.Fax
 www.timesmicrowave.com

EZ-400-TM-RP
Reverse Polarity TNC Male (female pin)
for LMR-400 Cable

Size A	CAGE CODE 68999	Drawing No.: 3190-794
-----------	---------------------------	---------------------------------

Scale: NA	Rev. ()	Sheet: 1 of 1
-----------	----------	---------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[EZ-400-TM-RP](#)