







PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL

PC BOARD VERSIONS		
PRODUCT NR:	PCB THICKNESS	DIM A
85864-X02	1.6	2.90
85864-X12	2.4	3.53



- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
  - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
  - 3 INDICATED HOLES ARE UNPLATED.
  - 4 For PLATING SPEC, REFER TO DRAWING 10097866.
  - 5 PRODUCTMARKING: PART NUMBER & BATCH ID.
  - 6 SET BACK FOR TAIL BLOCK
  - 7 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
  - 8 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD.
  - 9 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
  - 10 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		ELECTRONICS	
SEE NOTES						www.falconconnect.com	
ltr	ecm no	dr	date	projection	title		
H	DF09-0088	Cent	03/03/09	Linear	5 ROW R.A. S.T.B. SIGNAL RECEPT. 24mm MOD.P.P.		
C	V00578	LLA	000316	angles	product family		
D	V00850	GNV	000512	dr	size		
E	pg04-0104	CLU	041223	engr	dwg no		
F	pg07-0169	Cent	05/15/07	chr	scale		
G	pg08-0171	TER	08/15/08	app	5:1		
sheet	revision						
index	sheet						

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[85864-102LF](#) [85864-112LF](#) [85864-312LF](#)