




Notes:

- 1. Electrical Specifications:
 - Meets USB 2.0 Specification
 - Contact Resistance: 30 mOhm max.
 - Insulation Resistance: 1000 MOhm min. @ 100 VDC
 - Current Rating: 1.5 A max. at 25°C
 - Working Voltage: 30 V (RMS) max.
 - DWV: 500 VAC/60s at sea level
 - Operating Temperature: -40°C to +85°C

2. Material and Finish:

- Receptacle Housing and Protective Cover: Polyester, UL94 V-0, Color: Black
- ② or ABS, Nickel Plated, UL94 V-0
- Panel Nut: Brass, Finish: Nickel Plated
- Panel and Cover Gasket: Silicon, Color: White
- Tether: Polycarbonate, Color: Black
- USB Adaptor Insulator: PBT, UL94 V-0, Black
- USB Adaptor Metal Shell: Copper Alloy, Nickel Plated
- USB Adaptor Overmold material: PBT UL94 V-0, Color: Black
- USB Contacts: Copper Alloy, Finish: 30 u" Gold min. over Nickel

3. Connector can be mounted to a maximum panel thickness of 3.2 mm.
4. IP67 rated when covered or fully mated with the appropriated mating connector

(b)	Version	Part Number
(c)	Plastic Version	17-210141
	Metallized Plastic Version	17-210181

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. CONECSHIP AND COPYRIGHT OF CONEC CORPORATION DO NOT ALTER CAD DRAWING BY HAND	Customer:				Tolerance Unless otherwise specified 0 PLC ± 0.50 1 PLC ± 0.38 2 PLC ± 0.25 3 PLC ± 0.10 ANGLES $\pm 3^\circ$				Scale:		Dim. in mm	
	Name		Title		Approval Date		Autodesk Inventor		Material: See Notes			
									Receptacle + Cover Assembly Kit Both Sides Bayonet Receptacle Housing with USB Type A F/F Adaptor			
					2012	Date	Name					
					Draw.	Sept. 28	Vincent Ke					
					Appd.	Sept. 28	J. Chaudry					
					Norm							
	c	3 x c	Jan/18/2013	Vincent Ke	D-old							
	b	1 x b	Oct/17/2012	Vincent ke			Drawing No.: 17K1A357				DIN A3	
a	original			Part No.: SEE PART NUMBER TABLE				Sheet 1/1				
Rev.	Changes	Date	Name									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[17-210141](#)