









| PRODUCT NUMBER<br>("LF" DENOTES LEAD-FREE) | CONTACT<br>PLATING<br>NOTE | MATING LENGTH, DIM "X" |        |        |        | ROHS<br>COMPATIBILITY |
|--------------------------------------------|----------------------------|------------------------|--------|--------|--------|-----------------------|
|                                            |                            | POSN 1                 | POSN 2 | POSN 3 | POSN 4 |                       |
| 10028916-4444P00                           | 2                          | 1.10                   | 1.10   | 1.10   | 1.10   | N/A                   |
| 10028916-4444P00LF                         | 3                          |                        |        |        |        | SEE NOTE 9            |
| 10028916-5555P00                           | 2                          | 2.60                   | 2.60   | 2.60   | 2.60   | N/A                   |
| 10028916-5555P00LF                         | 3                          |                        |        |        |        | SEE NOTE 9            |
| 10028916-4555P00                           | 2                          | 1.10                   | 2.60   | 2.60   | 2.60   | N/A                   |
| 10028916-4555P00LF                         | 3                          |                        |        |        |        | SEE NOTE 9            |
| 10028916-5455P00                           | 2                          | 2.60                   | 1.10   | 2.60   | 2.60   | N/A                   |
| 10028916-5455P00LF                         | 3                          |                        |        |        |        | SEE NOTE 9            |
| 10028916-5545P00                           | 2                          | 2.60                   | 2.60   | 1.10   | 2.60   | N/A                   |
| 10028916-5545P00LF                         | 3                          |                        |        |        |        | SEE NOTE 9            |
| 10028916-5554P00                           | 2                          | 2.60                   | 2.60   | 2.60   | 1.10   | N/A                   |
| 10028916-5554P00LF                         | 3                          |                        |        |        |        | SEE NOTE 9            |
| 10028916-4554P00                           | 2                          | 1.10                   | 2.60   | 2.60   | 1.10   | N/A                   |
| 10028916-4554P00LF                         | 3                          |                        |        |        |        | SEE NOTE 9            |
| 10028916-4455P00                           | 2                          | 1.10                   | 1.10   | 2.60   | 2.60   | N/A                   |
| 10028916-4455P00LF                         | 3                          |                        |        |        |        | SEE NOTE 9            |
| 10028916-5544P00                           | 2                          | 2.60                   | 2.60   | 1.10   | 1.10   | N/A                   |
| 10028916-5544P00LF                         | 3                          |                        |        |        |        | SEE NOTE 9            |
| 10028916-5445P00                           | 2                          | 2.60                   | 1.10   | 1.10   | 2.60   | N/A                   |
| 10028916-5445P00LF                         | 3                          |                        |        |        |        | SEE NOTE 9            |



|               |                                                                                       |         |       |      |                                                                                       |          |                              |                                                                                       |                                                                                       |        |                |                |                |     |           |
|---------------|---------------------------------------------------------------------------------------|---------|-------|------|---------------------------------------------------------------------------------------|----------|------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--------|----------------|----------------|----------------|-----|-----------|
| spec ref      | GS-12-220                                                                             |         |       | dr   | Chen-Hong Tan                                                                         |          | 2005/08/04                   |  |  | size   | A2             | scale          | 6:1            |     |           |
| tolerance std | TOLERANCES UNLESS OTHERWISE SPECIFIED                                                 |         |       | eng  | Terry Luo                                                                             |          | 2021/05/27                   |                                                                                       |                                                                                       | ecn no | ELX-DG-41001-1 |                |                |     |           |
| ASME Y14.5    |                                                                                       |         |       | chr  | -                                                                                     |          | -                            | appr                                                                                  | Heaven Cen                                                                            |        | 2021/06/03     | product family | 2mm High Power |     | rel level |
| surface 3.2   |  | linear  | 0.X   | ±.3  |  | title    | 2X2 VERTICAL RECEPTACLE ASSY |                                                                                       |                                                                                       |        | dwg no         | 10028916       |                | rev | N         |
|               |                                                                                       |         | 0.XX  | ±.1  |                                                                                       |          |                              |                                                                                       |                                                                                       |        |                |                |                |     |           |
|               |                                                                                       |         | 0.XXX | ±.05 |                                                                                       |          |                              |                                                                                       |                                                                                       |        |                |                |                |     |           |
| ASME Y14.5    |                                                                                       | angular | 0°    | ±2°  |                                                                                       | cat. no. | -                            | Product - Customer Drw                                                                |                                                                                       |        |                | sheet 1 of 2   |                |     |           |



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10028916-4455P00](#) [10028916-5455P00](#) [10028916-5545P00](#) [10028916-5554P00](#) [10028916-4444P00](#) [10028916-5555P00](#)