




rev	ecn no	dr	date
A	CONVERSION REVISION 01	KN	14-09-01
B	DG05-0278	Kason	05-08-05
C	DG07-0362	Kason	05-09-07

		www.fciconnect.com				tolerance 1DEC +0.2 1DEC 2DEC +0.1 2DEC ANGLES ±1° HD EKEN		projection 			
Dr	M.FRET	11-07-00	Product family		MILLIPICS		size	A4		Scale	
Eng			Spec ref							3/1	
Chr			Material					ECN			
Appr											
MPACS 8+2R RA RCP CONN TYPE DE/UPPER SHIELDED							drawing no BS,C ,202258,010		Rev C		
catalog no			HM2R95PA8100----				CUMSTOMER			sheet 1 of 1	



PERFORMANCE CHARACTERISTICS

CURRENT RATING 1.5A AT 20°C (FULLY LOADED)

RATED VOLTAGE : 500 V AC (CONT /CONT)

OPERATING TEMPERATURE : -55°C TO 125°C

CONTACT RESISTANCE 20 mΩ MAX

INSERTION FORCE : 0.75N MAX/CONT

EXTRACTION FORCE : 0.15N MIN/CONT

INSULATION RESISTANCE : 10^4 M Ω MIN

NOTES 1. 

2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.

3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :
BS.A.201572.001

4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[HM2R95PA8100N9LF](#) [HM2R95PA8100Z1LF](#) [HM2R95PA8100E9LF](#)