




C	ZINC DIECAST BODY AND HEAD WITH STEEL COVER, BODY AND COVER FINISHED IN RED EPOXY PAINT HEAD FINISHED IN BLACK EPOXY PAINT
D	RED GLASS FILLED POLYESTER HOUSING AND COVER, ZINC DIECAST HEAD FINISHED IN BLACK EPOXY PAINT
E	ZINC DIECAST BODY AND HEAD WITH STEEL COVER, BODY AND COVER FINISHED IN RED EPOXY PAINT, HEAD FINISHED IN BLACK EPOXY PAINT 3 - CONDUIT

A	1/2" NPT X 1/4 CONDUIT THREAD ADAPTER REQUIRED FOR GSD AND GSE PRODUCT
	1/2" NPT X 1/4 CONDUIT THREAD GSA PRODUCT
	PG 13.5 CONDUIT THREAD NO ADAPTER REQUIRED
	M20 X 1.5 CONDUIT THREAD ADAPTER REQUIRED WITH GSD PRODUCT ONLY
B	PF 1/2 CONDUIT THREAD ADAPTER REQUIRED WITH GSD PRODUCT ONLY

AVAILABLE IN GSC, GSD, AND GSE		AVAILABLE IN GSE ONLY	
01	SNAP-ACTION CONTACTS	40	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
07	SNAP-ACTION CONTACTS (GOLD PLATED CONTACTS)	41	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
03	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)	42	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
33	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)	43	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
06	SLOW-ACTION CONTACTS (2 NORMALLY CLOSED)	44	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
36	SLOW-ACTION CONTACTS (2 NORMALLY CLOSED) (GOLD PLATED CONTACTS)	45	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
46	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)	47	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)



NOTES:

1 - MAXIMUM OPERATING TORQUE - 12 Nm / 1.1 in-lb

2 - MAXIMUM DISCONNECT TORQUE - 16 Nm / 1.5 in-lb

3 - MAXIMUM TIGHTENING TORQUE FOR FIXING SCREW - 0.5Nm/4.4in-lb (GSC & GSE PRODUCTS)

4 - 0.339Nm/3 in-lb (GSD PRODUCTS)

5 - IP66/IP67 NEMA 1,4X(INDOOR USE ONLY),12,13 FOR GSD PRODUCTS

ELECTRICAL RATING - I _{th} = 10A					ENVIRONMENTAL	APPROVALS
SILVER CONTACTS				GOLD PLATED CONTACTS	IP66 NEMA 1, 4, 12, 13 TEMP RANGE: -40°C TO +85°C -40°F TO +185°F STORAGE: -40°C TO +85°C -40°F TO +185°F SHOCK: 50G PER IEC 68-2-27 VIBRATION: 100G PER IEC 68-2-6	  IEC 947-5-1 EN50047
AC FOR SWITCH CODES 01, 07, 03, 33	AC FOR SWITCH CODES 06, 36	AC FOR SWITCH CODES 40,41,42,43,44,45,46,47	DC			
A600 AC15 U _e I _e	A500 AC15 U _e I _e	A300 AC15 U _e I _e	Q300 DC13 U _e I _e			
VOLTS AMPS 120 6 240 3 380 1.9 480 1.5 500 1.4 600 1.2	VOLTS AMPS 120 6 240 3 380 1.9 480 1.5 500 1.4	VOLTS AMPS 120 6 240 3	VOLTS AMPS 125 0.55 250 0.27			
				1V 10uA MIN 50V 100mA MAX		

CONTACT CLOSED

CONTACT OPEN

** POSITIVE OPENING TO IEC 947-5-1

M	GS SERIES CHART 2
----------	--------------------------



THIRD ANGLE PROJECTION			
			
SCALE		FULL	
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DIMENSION UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 1/			
H/R	TOL	H/R	TOL
1/16	0.005	1/8	0.005
1/8	0.005	1/4	0.005
1/4	0.005	3/8	0.005
3/8	0.005	1/2	0.005
1/2	0.005	3/4	0.005
3/4	0.005	1	0.005
1	0.005	2	0.005
2	0.005	4	0.005
4	0.005	6	0.005
6	0.005	8	0.005
8	0.005	10	0.005
10	0.005	12	0.005
12	0.005	14	0.005
14	0.005	16	0.005
16	0.005	18	0.005
18	0.005	20	0.005
20	0.005	22	0.005
22	0.005	24	0.005
24	0.005	26	0.005
26	0.005	28	0.005
28	0.005	30	0.005
30	0.005	32	0.005
32	0.005	34	0.005
34	0.005	36	0.005
36	0.005	38	0.005
38	0.005	40	0.005
40	0.005	42	0.005
42	0.005	44	0.005
44	0.005	46	0.005
46	0.005	48	0.005
48	0.005	50	0.005
50	0.005	52	0.005
52	0.005	54	0.005
54	0.005	56	0.005
56	0.005	58	0.005
58	0.005	60	0.005
60	0.005	62	0.005
62	0.005	64	0.005
64	0.005	66	0.005
66	0.005	68	0.005
68	0.005	70	0.005
70	0.005	72	0.005
72	0.005	74	0.005
74	0.005	76	0.005
76	0.005	78	0.005
78	0.005	80	0.005
80	0.005	82	0.005
82	0.005	84	0.005
84	0.005	86	0.005
86	0.005	88	0.005

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[GSDA01S3](#) [GSEA41S1](#) [GSEA41S3](#)