

[illegible]

Technical drawing of a mechanical part with three detail views:

- DETAIL B:** Shows a cross-section of the part with dimensions: ± 0.15 , 4.2 , ± 0.1 , 4 , ± 0.03 , 0.45 , 1.65 , and ± 0.1 . A feature is labeled "FULL R".
- DETAIL A:** Shows a cross-section of the part with dimensions: ± 0.15 , 4 , ± 0.1 , 1 , and 1.65 . A feature is labeled "FULL R".
- DETAIL C:** Shows a cross-section of the part with dimensions: 0 , -0.2 , $2-0.25$, $(\text{NOTE } 2)$, $2-0.25$, $(\text{NOTE } 2)$, and 0 .

4	LATCH 2	1	STAINLESS	TIN PLATING		
5	LATCH 1	1	STAINLESS	TIN PLATING		
3	INSULATOR	1	GLASS FILLED LCP			
2	LOWER CONTACT	102	COPPER ALLOY	CONTACT AREA: Au(0.1μm MIN) OVER NICKEL SOLDERING AREA: GOLD FLASH OVER NICKEL		
1	UPPER CONTACT	102	COPPER ALLOY	CONTACT AREA: Au(0.1μm MIN) OVER NICKEL SOLDERING AREA: GOLD FLASH OVER NICKEL		
符号 NO.	名称 DESCRIPTION	個数 QTY.	材料 MATERIAL	仕上 FINISH	備考 REMARKS	
仕様書(SPECIFICATION) JACS-10662		第1版(ORIGINAL DATE) 24.Aug.2010		尺(SCALE) 2:1	シリーズ(SERIES) MM80	
公差(GENERAL TOLERANCE)		製図 DR.		名称(TITLE)	日本航空電子工業株式会社	
寸法(DIMENSION)		担当 CHK.	R.KATOU	MM80-204B1-1R	JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.	
角度(ANGLES)		盗用 APPD.			図面番号(DRAWING NO.)	版数 (REV.)
. ±0.8		承認 APPD.	T.SHINDOU			
.X ±0.4						
.XX ±0.1						
.XXX ±						
				質量(MASS)		
						SJ110255



KEYING CENTER

1.65

±0.4

1.35

Z

[illegible]

略品名

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[MM80-204B1-1](#)