




PART NUMBER 10106263-D006001LF



Copyright FCI. FCI

spec ref	*	dr	Peng-Bing Fu	2012/02/22	projection	MM	size	A3	scale	3:2													
tolerance std	ASME Y14.5	eng	Rainbow Zhan	2015/09/21			ecn no	ELX-DG-21977-1															
TOLERANCES UNLESS OTHERWISE SPECIFIED		chr	Fancy Zhang	2015/09/25			product family	PwrBlade+		rel level	Released												
surface	<table border="1"> <tr> <td>linear</td> <td>0.X</td> <td>±0.5</td> </tr> <tr> <td></td> <td>0.XX</td> <td>±0.25</td> </tr> <tr> <td></td> <td>0.XXX</td> <td>±0.10</td> </tr> <tr> <td>ASME Y14.5</td> <td>angular</td> <td>0°</td> <td>±2°</td> </tr> </table>	linear	0.X	±0.5				0.XX	±0.25		0.XXX	±0.10	ASME Y14.5	angular	0°	±2°	appr	Pei-Ming Zheng	2015/09/25	part no	13HP + 24S	dwg no	10106263-D006001
linear	0.X	±0.5																					
	0.XX	±0.25																					
	0.XXX	±0.10																					
ASME Y14.5	angular	0°	±2°																				
		www.fci.com		cat. no.	Product - Customer Drw			sheet 1 of 3															

PRODUCT NO. 10106263-D006001LF	ROWS DCBA	HIGH POWER													SIGNAL					
		E1	P1	P2	P3	P4	P5	P6	P7	P8	P9	P10	P11	P12	P13	1	2	3	4	5



CODE	DESCRIPTION
HA	METAL HOLD DOWN
HE	STD HIGH POWER CONTACT (3.05)
LB	LMFB SIGNAL CONTACT, ROW B (3.05)
LC	LMFB SIGNAL CONTACT, ROW C (3.05)
LD	LMFB SIGNAL CONTACT, ROW D (3.05)
SA	STD SIGNAL CONTACT, ROW A (3.05)
SB	STD SIGNAL CONTACT, ROW B (3.05)
SC	STD SIGNAL CONTACT, ROW C (3.05)
SD	STD SIGNAL CONTACT, ROW D (3.05)

dr	Peng-Bing Fu	2012/02/22	projection	MM	size	A3	scale	3:2
eng	Rainbow Zhan	2015/09/21			ecn no	ELX-DG-21977-1		
chr	Fancy Zhang	2015/09/25	product family	PwrBlade+	rel level	Released		
appr	Pei-Ming Zheng	2015/09/25						
www.fci.com		cat. no.	13HP + 24S RA PRESS-FIT HEADER		dwg no	10106263-D006001	rev	C
Product - Customer Drw				sheet 2 of 3				

Copyright FCI.

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE P/N CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENSIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ± 0.025 MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ± 0.07 MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.
- $\triangle B$ 9) A $\triangle B$ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.



Copyright FCI.

dr	Peng-Bing Fu	2012/02/22	projection 	MM 	size	A3	scale	3:2	
eng	Rainbow Zhan	2015/09/21			ecn no	ELX-DG-21977-1			
chr	Fancy Zhang	2015/09/25	product family	PwrBlade+	rel level	Released			
appr	Pei-Ming Zheng	2015/09/25			title	13HP + 24S RA PRESS-FIT HEADER		dwg no	10106263-D006001
www.fci.com			cat. no.	Product - Customer Drw			sheet 3 of 3		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10106263-D006001LF](#)