




Amphenol
FCi

© 2016 AFCi

spec ref -		dr Sandar Soe		2012/09/13	projection	MM	size A2	scale 5:1
tolerance std ASME Y14.5	TOLERANCES UNLESS OTHERWISE SPECIFIED	eng Terry Luo		2020/09/08			ecn no ELX-DG-38252-1	
		chr -		-				
		appr Heaven Cen		2020/09/17			product family AIRMAX VS	rel level Released
surface -		Amphenol FCI		title AIRMAX VS2 VERTICAL HEADER 4 PAIR 120 POS 2MM 10 COL,GXT+			dwg no 10122770	rev D
ASME Y14.5	linear	0.X	±0.3					
		0.XX	±0.10					
		0.XXX	±0.050					
	angular	0°	±2°		cat. no. -	Product - Customer Drw		sheet 1 of 4

PDS: Rev :D

STATUS:Released

Printed: Sep 18, 2020


(22.40)
PROTECTIVE CAP WIDTH


(16.45)

VIEWS SHOWN WITH
PROTECTIVE COVER INSTALLED
10122770-1*1LF

NOTE 12

NOTE 13

spec ref -				dr	Sandar Soe	2012/09/13	projection 	MM 	size	A2	scale	5:1
tolerance std				eng	Terry Luo	2020/09/08			ecn no	ELX-DG-38252-1		
ASME Y14.5				chr	-	-		product family	AIRMAX VS	rel level	Released	
-				appr	Heaven Cen	2020/09/17						
surface -  ASME Y14.5	linear	0.X	±0.3	Amphenol FCI title AIRMAX VS2 VERTICAL HEADER 4 PAIR 120 POS 2MM 10 COL,GXT+	dwg no 10122770			rev D				
		0.XX	±0.10									
		0.XXX	±0.050									
angular	0°	±2°	cat. no.		-	Product - Customer Drw			sheet 2 of 4			



Amphenol
FCi

© 2016 APCI

spec ref -		dr Sandar Soe		2012/09/13	projection 	MM 	size A2	scale 3:1
tolerance std		eng Terry Luo		2020/09/08			ecn no ELX-DG-38252-1	
ASME Y14.5 -		chr -		2020/09/17			rel level Released	
		appr Heaven Cen			product family AIRMAX VS			
surface -  ASME Y14.5	linear	0.X	±0.3	Amphenol FCI	title AIRMAX VS2 VERTICAL HEADER 4 PAIR 120 POS 2MM 10 COL,GXT+		dwg no 10122770	rev D
		0.XX	±0.10					
		0.XXX	±0.050					
	angular	0°	±2°		cat. no. -	Product - Customer Drw		sheet 3 of 4

PDS: Rev :D

STATUS:Released

Printed: Sep 18, 2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10122771-1011LF](#) [10122770-1021LF](#)