









PRODUCT NUMBER	DIM A	DIM B	NOTES
84620-101	10.00	11.88	TOOLED
84620-101LF	10.00	11.88	
84620-102	22.00	23.88	NOT TOOLED
84620-103	34.00	35.88	
84620-104	46.00	47.88	
84620-105	58.00	59.88	
84620-106	70.00	71.88	

#### NOTES:

- SEE APPLICATION SPECIFICATION GS-20-010 FOR INFORMATION ON AVAILABLE TOOLING, CIRCUIT BOARD DESIGN CONSIDERATIONS, REPAIR PROCEDURES AND PRODUCT OFFERINGS.
- UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5, 1994.
- HOUSING MATERIAL: LIQUID CRYSTAL POLYMER, 30% GLASS FILLED, FLAME RETARDANT PER UL 94-V0.
- TEMPERATURE RANGE: -55°C TO +105°C.
- THE PRODUCTS WHERE THE PART NUMBERS END IN LF AND NON LF PARTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260° FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN. FOR LEAD FREE PART NUMBERS, ADD "LF" SUFFIX. EXAMPLE: 84620-101LF.



mat'l code SEE NOTE 3				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com			
ltr	ecn no.	dr	date	linear	0.X ±0.3		COPY			titleVERTICAL SIGNAL HDR SHROUD 5 ROW, PRESS-FIT, STANDARD	
A	V21194	TAB	2002-07-22		0.XX ±0.13						
B	V06-0107	DAI	2006-02-22		0.XXX ±0.051						
C	V06-0544	DCH	2006-06-12	angles	0° ±2°						
D	V07-0693	HTB	2007-11-27	dr	T.BRUNGARD	2002-07-17					
				enrg	J. VOLSTORF	2001-02-25					
				chr	M. STRAWSER	2002-07-17				product familyMETRAL 1000/2000	code213
				appd	M. STRAWSER	2002-07-17					
							scale2:1		A	84620	1 of 1
sheet index	revision sheet	D	I								

Pro/E

cage code 22526

PDM: Rev:D

STATUS: Released Printed: May 13, 2011

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[84620-101LF](#)