


P.C.B Layout
Top view



SECTION P-P

$$\begin{aligned} \text{DimL} &= (N/2 - 1) \times 3.5 + 4.30 \\ \text{DimB} &= (N/2 - 1) \times 3.5 \\ \text{DimC} &= (N/2 - 1) \times 3.5 \end{aligned}$$

N=Number of poles

POLES	Dim. Tol	Dim.L/B/C
2x2p-2x6p		±0.15
2x7p-2x12p		±0.25
2x13p-2x18p		±0.30
2x19p-2x24p		±0.35

SIGN	DATE	DESCRIPTION	APPROVER
△	11/04/14	change the product description	Airy min
△			
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Terminal housing: LCP (UL94V-0)
- Item ② Male contact pin: Copper, Matte Tin plated

Electrical: cULus

- Voltage rating: 300V
- Current rating: 5.5A
- Withstanding Voltage: 1.3KV
- Operating temperature: -45°C to +65°C
- Reflow Soldering temperature: 260°C/10 Sec max.
- Safety Approval: cULus
- Critical dimension: ▽



NR xx 1 1 x 0 xxxx G

No. OF POLES
04: 2x2 POLES
06: 2x3 POLES
:
48: 2x24 POLES

COLOR
0: BLACK

RoHS compliant
(lead<4%)
In copper Alloy

00G0: "@" Logo (Standard)
00GA: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NR 3.5mm series close vertical (THR type)			
PART NO.	NRxx11x0xxxxG		DWG NO.	8NR0004
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.
 Airy min 2014.12.18		 Airy min 2014.12.18		Tolerance X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
				UNIT: mm SCALE: NONE SHEET: 01/01 REV.: B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[NR12110000G0G](#) [NR0611000000G](#) [NR08110000G0G](#) [NR10110000G0G](#) [NR04110000G0G](#)