








NOTE7. LOT NUMBER IS MARKED AS INDICATED.  
 【AUTOMATIC MACHINE ASSEMBLY】 : WITH LOT NUMBER  
 【MANUAL JIG ASSEMBLY】 : WITHOUT LOT NUMBER

△ (EX) A5 J 5 6 1 1

MODIFICATION MARK △

VENDER ID

YEAR (END OF ONE DIGIT AT A. D.)

MONTH (JAN. TO SEP. :1 TO 9, OCT. :0, NOV. :X, DEC. :Y)


DAY (NUMBER OR ALPHABET)

EQUIPMENT No. (NUMBER OR ALPHABET)

NOTE8. RECOMMEND TO UTILIZE THE SIDE SHELL TABS BY SOLDERING TO PCB PADS FOR THE MECHANICAL STRENGTH AND GND CONNECTION.  
NOTE9. LASER WELD POINTS MAY BE DISCOLORED.

|         |     |      |      |                  |                   |    |    |      |                  |      |      |     |
|---------|-----|------|------|------------------|-------------------|----|----|------|------------------|------|------|-----|
| Pin No. | A12 | A11  | A10  | A9               | A8                | A7 | A6 | A5   | A4               | A3   | A2   | A1  |
|         | GND | RX2+ | RX2- | V <sub>bus</sub> | SBU1              | D- | D+ | CC   | V <sub>bus</sub> | TX1- | TX1+ | GND |
|         |     |      |      |                  |                   |    |    |      |                  |      |      |     |
|         | GND | TX2+ | TX2- | V <sub>bus</sub> | V <sub>CONN</sub> |    |    | SBU2 | V <sub>bus</sub> | RX1- | RX1+ | GND |
| Pin No. | R1  | R2   | R3   | R4               | R5                | R6 | R7 | R8   | R9               | R10  | R11  | R12 |

|   |               |    |                        |                                                                                                             |                                                                                                                                                           |
|---|---------------|----|------------------------|-------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
| 8 | CAP           | 1  | HEAT RESISTING PLASTIC | (BLACK)                                                                                                     | HALOGEN-FREE                                                                                                                                              |
| 7 | TAPE          | 2  | POLYIMIDE              | —                                                                                                           | HALOGEN-FREE                                                                                                                                              |
| 6 | SHELL         | 1  | STAINLESS STEEL        | NICKEL PLATING                                                                                              | NICKEL: 1 $\mu$ m MIN.                                                                                                                                    |
| 5 | GROUND SPRING | 2  | STAINLESS STEEL        | NICKEL PLATING                                                                                              | NICKEL: 0.8 $\mu$ m MIN.                                                                                                                                  |
| 4 | LOCK SPRING   | 1  | STAINLESS STEEL        | NICKEL PLATING                                                                                              | NICKEL: 0.8 $\mu$ m MIN.                                                                                                                                  |
| 3 | INSULATOR B   | 2  | HEAT RESISTING PLASTIC | (BLACK)                                                                                                     | HALOGEN-FREE                                                                                                                                              |
| 2 | INSULATOR A   | 1  | HEAT RESISTING PLASTIC | (BLACK)                                                                                                     | HALOGEN-FREE                                                                                                                                              |
| 1 | CONTACT       | 24 | COPPER ALLOY           | CONTACT AREA;<br>GOLD FLASH OVER PALLADIUM-NICKEL<br>OVER NICKEL<br>SOLDER TAILS;<br>GOLD FLASH OVER NICKEL | CONTACT AREA<br>NICKEL: 2 $\mu$ m MIN.<br>PALLADIUM-NICKEL: 0.75 $\mu$ m MIN.<br>GOLD FLASH: 0.05 $\mu$ m MIN.<br>SOLDER TAILS;<br>NICKEL: 2 $\mu$ m MIN. |

|                          |                   |                |                                    |                   |                                                                                                                                                |
|--------------------------|-------------------|----------------|------------------------------------|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| 符号<br>NO.                | 名称<br>DESCRIPTION | 個数<br>QTY.     | 材料<br>MATERIAL                     | 仕上<br>FINISH      | GOLD FLASH: 0.03 μm MIN.<br>備考<br>REMARKS                                                                                                      |
| 仕様書 (SPECIFICATION)      |                   |                | 第1版 (ORIGINAL DATE)<br>19/MAY/2017 | 尺度 (SCALE)<br>5:1 | シリーズ (SERIES)<br>DX07                                                                                                                          |
| JACS-30353<br>JAHL-30353 |                   |                | 製図<br>DR.                          | —                 | 日本航空電子工業株式会社                                                                                                                                   |
| 一般公差 (GENERAL TOLERANCE) |                   |                | 担当<br>CHK.                         | K. UEDA           |  <b>JAPAN AVIATION<br/>ELECTRONICS<br/>INDUSTRY, LTD.</b> |
| 寸法 (DIMENSION)           |                   | 角度 (ANGLES)    | 査閲<br>APPD.                        | —                 |                                                                                                                                                |
| ×0 ±0.8                  |                   | ×° ±           | 承認<br>APPD.                        | Y. SAITOU         |                                                                                                                                                |
| ×× ±0.4                  |                   | ××° ±          |                                    |                   |                                                                                                                                                |
| ××× ±0.1                 |                   |                |                                    |                   | 図面番号 (DRAWING NO.)                                                                                                                             |
| ××××                     |                   | 単位 (UNIT) : mm |                                    | 質量 (MASS)         | <br>SJ118710                                              |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[DX07P024AJ5R1500](#)