

G2-LAURA-O-WAS-P

Asymmetric oval beam for wall-washing.
Assembly with thinner white holder, installation
tape and location pins.

TECHNICAL SPECIFICATIONS:


Dimensions	21.6 mm
Height	13.1 mm
Fastening	tape, pin
ROHS compliant	yes ⓘ


MATERIAL SPECIFICATIONS:

Component	Type	Material	Colour	Finish
LAURA-O-WAS	Single lens	PMMA	clear	
LAURA-LT-PIN-XP-HLD-WHT	Holder	PC	white	
ROSE-TAPE	Tape	PU tape	black	

ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CA13638_G2-LAURA-O-WAS-P	Single lens	1440	360	180	5.9
» Box size: 451 x 254 x 152 mm					









PHOTOMETRIC DATA (MEASURED):




LED XB-D
FWHM Asymmetric
Efficiency 87 %
Peak intensity 4 cd/Im
LEDs/each optic 1
Light colour White
Required components:





LED XP-E2
FWHM Asymmetric
Efficiency 88 %
Peak intensity 4.8 cd/Im
LEDs/each optic 1
Light colour White
Required components:



LED XP-G
FWHM Asymmetric
Efficiency 84 %
Peak intensity 2.6 cd/Im
LEDs/each optic 1
Light colour White
Required components:





LED XP-G2
FWHM Asymmetric
Efficiency 88 %
Peak intensity 3.7 cd/Im
LEDs/each optic 1
Light colour White
Required components:





PHOTOMETRIC DATA (MEASURED):





LED XT-E
FWHM Asymmetric
Efficiency 87 %
Peak intensity 3.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED LUXEON A
FWHM Asymmetric
Efficiency 86 %
Peak intensity 3.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED NVSW219F
FWHM Asymmetric
Efficiency 94 %
Peak intensity 3.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED OSLOM Square EC
FWHM Asymmetric
Efficiency 87 %
Peak intensity 3.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:




PHOTOMETRIC DATA (SIMULATED):



LED LUXEON 3535L
 FWHM Asymmetric
 Efficiency 89 %
 Peak intensity 2.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED NVSxx19B/NVSxx19C
 FWHM Asymmetric
 Efficiency 88 %
 Peak intensity 2.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salu, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ledil:

[CA13638_G2-LAURA-O-WAS-P](#)