


## LARISA-M-PIN

~30° medium beam and holder with location pins

## SPECIFICATION:

Dimensions	9.9 x 9.9
Height	7.5 mm
Fastening	glue, pin
ROHS compliant	yes ⓘ




## MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
LARISA-M	Single lens	PMMA	clear		
LARISA-HOLDER-PIN	Holder	PC	black		

## ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CP15305_LARISA-M-PIN	Single lens	10000	300	100	7.1
» Box size: 300 x 250 x 250 mm					





See also our general installation guide: [www.ledil.com/installation\\_guide](http://www.ledil.com/installation_guide)

#### OPTICAL RESULTS (MEASURED):





LED XD16  
 FWHM / FWTM 27.0° / 57.0°  
 Efficiency 74 %  
 Peak intensity 2.2 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files





LED XQ-E HD  
 FWHM / FWTM 25.0° / 53.0°  
 Efficiency 86 %  
 Peak intensity 3 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files



LED XQ-E HI  
 FWHM / FWTM 19.0° / 45.0°  
 Efficiency 80 %  
 Peak intensity 3.8 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:





Light distribution files

#### OPTICAL RESULTS (MEASURED):





LED LUXEON Z  
FWHM / FWTM 21.0° / 46.0°  
Efficiency 82 %  
Peak intensity 3.7 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files





LED NCSxE17A  
FWHM / FWTM 26.0° / 57.0°  
Efficiency 69 %  
Peak intensity 2.1 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files



LED NVSxE21A  
FWHM / FWTM 29.0° / 29.0°  
Efficiency 66 %  
Peak intensity 1.7 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:





Light distribution files

### OPTICAL RESULTS (MEASURED):

**OSRAM**  
Opto Semiconductors

LED	OSLON SSL 80
FWHM / FWTM	25.0° / 56.0°
Efficiency	82 %
Peak intensity	2.9 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

### OPTICAL RESULTS (SIMULATED):



LED	LUXEON Rubix
FWHM / FWTM	22.0° / 43.0°
Efficiency	95 %
Peak intensity	5 cd/Im
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

### GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

### MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### LEDiL Oy

Joensuunkatu 7  
FI-24240 SALO  
Finland

#### LEDiL Inc.

228 West Page Street  
Suite D  
Sycamore IL 60178  
USA

#### Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B  
Casic Motor Building  
Shenzhen 518057  
P.R.CHINA

#### Local sales and technical support

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)

#### Shipping locations

Poznan, Poland  
Hong Kong, China

#### Distribution Partners

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ledil:](#)

[CP15305\\_LARISA-M-PIN](#)