

0496 0496-0-15-XX-23-XX-10-0 Press-fit in .106 mounting hole	0368 0368-0-33-XX-13-XX-10-0 Wire Crimp Termination. Accepts wire sizes 16 AWG Max. / 20 AWG Min.	8067 8067-0-19-XX-13-XX-10-0 Wire Crimp Termination. Accepts wire sizes 24 AWG Max. / 28 AWG Min.	1105 1105-0-15-XX-13-XX-04-0 Press-fit in .080 mounting hole
8730 8730-0-19-XX-23-XX-10-0 Wire Crimp Termination. Accepts wire sizes 22 AWG Max. / 26 AWG Min.	3667 3667-0-19-XX-23-XX-10-0 Wire Crimp Termination. Accepts wire sizes 18 AWG Max. / 22 AWG Min.	9372 9372-0-15-XX-23-XX-10-0 Solder mount in .102 min. mounting hole	4582 4582-0-15-XX-23-XX-10-0 Square press-fit in .040 plated thru hole
5834 5834-0-15-XX-23-XX-10-0 Press-fit in .107 mounting hole	9401 9401-0-15-XX-23-XX-10-0 Solder mount in .102 min. mounting hole Also available on 24mm wide carrier tape: 1,100 parts per 13" reel. Order as: 9401-0-57-XX-23-XX-10-0	9801 9801-0-15-XX-23-XX-10-0 Solder mount in .102 min. mounting hole Also available on 16mm wide carrier tape: 1,200 parts per 13" reel. Order as: 9801-0-57-XX-23-XX-10-0	8829 8829-0-15-XX-23-XX-10-0 Solder mount in .102 min. mounting hole
SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°	ORDER CODE: XXXX - X - XX - XX - XX - XX - 0 BASIC PART # → SPECIFY SHELL FINISH: 01 200μ" TIN/LEAD OVER NICKEL 80 200μ" TIN OVER NICKEL (RoHS) 15 10μ" GOLD OVER NICKEL (RoHS) SPECIFY CONTACT FINISH: 01 200μ" TIN/LEAD OVER NICKEL 80 200μ" TIN OVER NICKEL (RoHS) 27 30μ" GOLD OVER NICKEL (RoHS) SELECT CONTACT #13 or #23 CONTACT (DATA ON PAGE 226)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

8067-0-19-01-23-01-10-0