



Main

Range of product	9012G
Pressure sensor type	Electromechanical pressure switch
Pressure sensor name	9012G
Pressure sensor size	150 psi
Maximum pressure	475 psi
Contacts type and composition	NC-NO, SPDT-DB, Form Z, snap action, silver nickel contacts
Controlled fluid	Air Hydraulic oil (-40...250 °F) Non-corrosive liquids Non-corrosive gas
Fluid connection type	0.25 inch 18 NPTF conforming to UL 508
Pressure switch type of operation	Regulation between 2 thresholds
Scale type	Adjustable differential
Local display	With range scale window

Complementary

Range on decreasing pressure	3...150 psi
Approx adjustable differential at mid range	6...30 psi +/- 2.5 % full scale
Cable entry	0.5 inch NPT conduit entrance
Terminal block type	4 screw terminals
Electrical connection	Screw-clamp terminals, AWG 22...AWG 12
Electrical circuit type	Control circuit
Local signalling	1 LED (clear) DC at 24 V
[In] rated current	2.75 A (Ue = 24 V DC)
Setting	Internal
Enclosure material	Die cast aluminium alloy 380
Pressure actuator	Diaphragm (nitrile (Buna-N))
Height	5.55 in
Depth	3.11 in
Width	3.5 in
Operating position	Any position
Materials in contact with fluid	Zinc plated steel Nitrile (Buna-N)
Short-circuit protection	10 A by gL (cartridge) overload and short-circuit protection
Operating rate	<= 120 cyc/mn
Mechanical durability	5000000 cycles
Repeat accuracy	4 %
Product weight	3 lb(US)

Environment

vibration resistance	2 gn conforming to IEC 68-2-6 (f = 40...150 Hz)
shock resistance	50 gn conforming to IEC 58-2-27
standards	CE UL 508 CSA C22.2 No 14
product certifications	CE CSA LR25490 class 3211 03 UL listed file E12158 CCN NKPZ and CCN NTHT
NEMA degree of protection	NEMA 4/4X/13 conforming to UL 50

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Not Green Premium product	Not Green Premium product
Will not be Compliant	Will not be Compliant
Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold
Available	Available
Available	Available
WARNING: This product can expose you to chemicals including:	WARNING: This product can expose you to chemicals including:
Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
For more information go to www.p65warnings.ca.gov	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9012GAW5G21V1](#)