





PANDUIT PART NUMBER	USED WITH CABLE TIES	DIMENSIONS				WEIGHT grams/100pcs
		'A'	'B' (REF)	'C'	'D' (REF)	
PUM-049- <u> </u>	M, I, S	16.5	6.6	13.8	7.2	33 g



SCALE 2:1

NOTES:

- SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, MATERIAL AND COLOR.
- (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
- APPLICATION SPECIFICATION:
HOLE DIAMETER: 4.6 - 4.9 mm
PANEL THICKNESS: 0.7 - 3.0 mm

CAD FILENAME/LAYERS		10B015CV/01_DC_GB0239ML_REV06	
		TINLEY PARK, ILLINOIS	
PUM-049 PUSH UMBRELLA MOUNT 049			
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE METRIC TOLERANCE: ±0.5MM			
DRAWN BY TMSA		SCALE 1:1 UNLESS NOTED	
DATE 8-11-06		DRAWING NO. GB0239ML	
CHK'D		DWG A SIZE	
MAT'L: NYLON 6/6			

6	3/08/11	BWG	MPH	CHANGED MATERIAL NOTE. REMOVED MATERIAL BOX FROM CHART.	GB0239ML	6	PBC		
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PUM-049-C0](#) [PUM-049-M0](#)