


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PLT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	9.0 (229)	250 (1112)	EXTRA HEAVY	1.6 (722)
PLT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	20.1 (511)	250 (1112)	EXTRA HEAVY	3.1 (1406)
PLT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	22.2 (564)	250 (1112)	EXTRA HEAVY	3.6 (1633)
PLT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	28.3 (719)	250 (1112)	EXTRA HEAVY	4.9 (2223)
PLT10EH	2.5 (63.5)	10.0 (254.0)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	34.2 (869)	250 (1112)	EXTRA HEAVY	5.8 (2631)
PLT12EH	2.5 (63.5)	12.0 (304.8)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	0.78 (19.8)	40.1 (1019)	250 (1112)	EXTRA HEAVY	6.5 (2931)

NOTES:

*1) SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

							TITLE							
							PAN-TY®NON-RELEASABLE - LASHING TIES							
							CUSTOMER DRAWING							
							ITEM REVISION NAME			W10001EG/01				
							DATASET FILE NAME			W10001EG/01-SS-6512_r10				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			MATERIAL:				
							.x ± .1 (2.5) .xxx ± .010 (.25) .xx ± .02 (.5) ANGLES ± - - -			NYLON 6/6				
							 THIRD ANGLE PROJECTION			DRAWING NUMBER:				
										SS-6512				
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY		DATE	CHK	SCALE	SHT 1 OF 1		SIZE
							L.VALDES		7-15-77	HVP	NONE			A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PLT6EH-C0](#) [PLT10EH-C](#) [PLT6EH-Q](#) [PLT6EH-C](#) [PLT10EH-Q0](#) [PLT12EH-Q0](#) [PLT2EH-Q0](#) [PLT5EH-C0](#) [PLT5EH-Q0](#) [PLT8EH-Q0](#) [PLT8EH-C](#) [PLT12EH-C](#) [PLT2EH-C](#) [PLT6EH-Q0](#) [PLT5EH-Q](#) [PLT2EH-C0](#) [PLT5EH-C](#) [PLT12EH-C0](#) [PLT10EH-C0](#) [PLT8EH-C0](#)