

## Cone Top Warning Signs



Cone sold separately

**Temporarily and quickly direct facility traffic.**

- Slips into top of any standard, flexible traffic cone
- Rugged, 0.060" plastic
- Same message both sides
- Weather- and fade-resistant
- 10" x 14"

UOM
Each



PBB0067



PBB0072



PBB0077



PBB0070



PBB0071



PBB0069



PBB0068



PBB0073



PBB0074

## Pennant Flag Tapes

**Attention-getting pennant flag tapes warn of hazardous areas.**

### Standard style

- 9" x 12" red, polyethylene plastic pennants
- Sewn onto durable cord - approx. 66" lead cord each end
- Ideal for indoor and temporary outdoor applications

### Heavy-Duty style

- Large 18" x 18" fluorescent orange 9-oz. vinyl laminated, nylon pennants
- Tough, tear-resistant
- Sewn onto high-tensile strength cord - approx. 20-ft. lead each end
- Ideal for extended periods outdoors, withstands harsh conditions

### OSHA-Compliant style

- Large 18" x 18", fluorescent orange 9-oz. vinyl laminated, nylon pennants
- Sewn onto heavy-duty reinforced chord that exceeds OSHA's 500 lb. tensile strength requirements
- Meets OSHA 1926.502(f)(2)(iv) withstanding the harshest conditions



Part No.	Description	No. of Pennants	UOM
<b>Standard</b>			
PBB0025	60-ft.	36	Each
<b>Heavy-Duty</b>			
PFM0038	83-ft.	15	Each
PBB0004	113-ft.	25	Each
<b>OSHA-Compliant Style</b>			
PFM0039	83-ft.	15	Each
PBB0003	113-ft.	25	Each

## Cones

**Brightly colored cones are ideal to mark hazardous areas.**



**Meets applicable MUTCD and State Standards**

- Durable, flexible spring-back design
- Molded PVC (Poly-Vinyl-Chloride) plastic
- UV stabilizers for fade resistance
- Stackable for easy transport and storage



Part No.	Height	Weight	UOM
<b>All Red/Orange - Standard</b>			
PBB0165	12"	1.5 lbs	Each
PBB0126	18"	3 lbs	Each
PBB0167	28"	7 lbs	Each
PBB0169	36"	10 lbs	Each
PBB0170	36"	12 lbs	Each
<b>All Red/Orange - w/ reflective collars</b>			
PBB0017	28"	7 lbs	Each
PBB0022	36"	12 lbs	Each
<b>Fluorescent Yellow/Green - Standard</b>			
PBB0166	18"	3 lbs	Each
PBB0168	28"	7 lbs	Each
PBB0171	36"	10 lbs	Each

## Universal Cone Adapter

**Universal Cone Adapter fits most standard traffic cones.**

- Quickly and easily mount signs, flags and lights
- Can also be used with rope or barricade tape to form various sized barriers

Orange No.	Yellow Part No.	UOM
PBB0065	PBB0066	Each



Sign and cone sold separately

## Plastic Barricade Tapes

**Quick and effective temporary way to section-off hazards and danger zones.**

- Bold warning message continuously repeated the length of the roll
- Lightweight, 0.003" polyethylene plastic
- Durable for indoor and outdoor environments
- Easily cut and secure with nails, tape, staples or tie-off
- 3" x 1000-ft.



**DANGER ASBESTOS HAZARD**

PBB0034

**DANGER DANGER**

PBB0041

**DANGER DO NOT ENTER**

PBB0076

**DANGER HIGH VOLTAGE**

PBB0040

**DANGER KEEP OUT**

PBB0037

**AUTHORIZED PERSONNEL ONLY**

PBB0038

**CAUTION CAUTION**

PBB0036

**CAUTION CUIDADO**

PBB0035

**CAUTION DO NOT ENTER**

PBB0030

**CAUTION BURIED ELECTRICAL LINE BELOW**

PBB0039

**CAUTION CONSTRUCTION AREA**

PBB0029

**CAUTION MEN WORKING ABOVE**

PBB0031

**CAUTION WET PAINT**

PBB0033

**CAUTION OPEN TRENCH**

PBB0032



PBB0042



PBB0175

**UOM**  
Roll



Comply with requirements of ANSI Z535.5-3.2

## Woven Barricade Tapes



**Mark off hazard areas with extra-strong, durable polypropylene tapes.**

- Woven polypropylene
- 300-lbs. tensile strength
- Chemical- and weather-resistant
- Ideal outdoor use
- Reusable
- 2" x 200-ft. rolls

Part No.	Color	UOM
PBB0173	Black/Red	Roll
PBB0174	Black/Yellow	Roll

## Barricade Rope

**Mark off restricted and hazardous areas with high visibility rope.**

- Twisted strands in two-tone, contrasting safety colors
- 5/16" diameter polypropylene
- Floats, resistant to mildew and light chemical exposure
- 600-ft. per roll



Black/Yellow Part No.	Magenta/Yellow Part No.	Red/White Part No.	UOM
PFM0005	PFM0006	PFM0007	Roll

## Reflective Plastic Barricade Tapes



**Get reflective visibility in low light areas.**

- 0.003" polyethylene tape
- Words alternate in black and reflective silver print
- 3" x 1000-ft.

**UOM**  
Roll

**CAUTION CAUTION CAUTION** PBB0023

**DANGER DANGER DANGER** PBB0024

## Free Standing Signs




## Set out free-standing signs to identify temporary hazardous conditions.

- Panels have message on both sides
- Rugged 0.125" thick high-impact plastic
- Folds flat for transport and storage
- 20"H x 12"W

UOM

Each


7" x 5" clear pocket for holding a tag or folded permit sheet.



PBB0075



PBB0097



PBB0099



PBB0100



PBB0098



PBB0101



PBB0108



PBB0058



PBB0087



PBB0092



PBB0093



PBB0094



PBB0095



PBB0091



PBB0096



PBB0103



PBB0105



PBB0104



PBB0089




PBB0090



PBB0102



PBB0088



PBB0107







PBB0106



## Reversible Free Standing Signs

Mark temporary hazards with lightweight plastic stand-up signs.

- Versatile - two signs in one!
- Rugged 0.125" thick high-impact plastic
- Economical - ideal for limited purposes or disposable for one-time use
- Flip and fold sign inside-out to reveal second message
- Lightweight, waterproof corrugated plastic with fold-and-insert-tab
- Stands 20"H x 12"W
- Carry handle cut-out on top
- Folds flat



UOM  
Each

## Molded 2-Sided Free Standing Signs




PBB0018

Open up floor signs to mark temporary hazards.

- Sturdy molded plastic to withstand elements indoors and outdoors
- Message on both sides of the 12"W x 25"H Free Standing Signs stand-up floor sign
- Easy-carry handle
- Sign folds flat for storage


UOM  
Each





### Unique, industrial design ideal for plant or facility.

- All-plastic, yellow, polyethylene post and base
- 3" dia. post stands 38"H with 16"W, low-profile fillable base
- Base has pre-drilled holes to secure to floor
- Snap lock ensures post will not pull out from base when lifted and moved
- Breaks down and stacks for compact storage
- Finishing cap and C-Hooks included
- Optional color striping in standard and specialty reflective, fluorescent, or glow-in-the-dark
- Connect several posts with 2" x 1" x 1/4" Plastic Chain Links sold separately by the foot



### Standard Yellow Post

Part No.	Height	UOM
PBB0149	38"	Each

## Striped Post

### Yellow Post w/ Standard Color Vinyl Stripe

Color	Code
Red	RED
Green	GRN
Black	BLK
White	WHT
Blue	BLU
Orange	ORN
Magenta	MAG

Add stripe color code after part number.  
Example: Part No. PBB0150 +  
Color Code MAG = PBB0150MAG

Part No.	Height	UOM
PBB0150	38"	Each

### Yellow Post w/ Specialty Color Vinyl Stripe

Color	Code
Reflective Red	RRED
Reflective Yellow	RYEL
Reflective White	RWHT
Fluorescent Red	REDF
Fluorescent Orange	ORNF
Fluorescent Green	GRNF
Glow-in-the-Dark	GLOW

Add specialty stripe color code after part number.  
Example: Part No. PBB0152 +  
Color Code RRED = PBB0152RRED

Part No.	Height	UOM
PBB0152	38"	Each



## Barrier Cone Bars



*Cones sold separately*

**In an immediate situation, deploy a bar – placed between two traffic cones – to create a quick and temporary visible barrier.**

- Portable, expandable barrier bar
- Ring-ends fit over traffic cones
- Expands up to 6 1/2-ft.
- Collapses to 4-ft. for storage and transport
- Available in two contrasting colors
- Reflective strips for visibility in low light conditions

Part No.	Color	UOM
PBB0078	Black/Yellow	Each
PBB0079	Orange/White	Each

## Ring Weight



Prevent post from easily tipping.  
Fill vinyl ring weight with water to add 3-lbs. for stability. The 11 3/4" x 1" ring weight fits and conceals inside the base of the post.

Part No.	UOM
PBB0148	Each

## Chain Links

- Lightweight, yet strong polyethylene plastic
- Each link measures 2" x 1" x 1/4"
- Alternating colors change every two feet
- Available by the foot up to 500-ft.
- Indoor and limited outdoor use



**To Order Chain Links:** Add color code after part number.

Example: Part No. PBB0115 + Color Code YEL = PBB0115YEL

Part No.	Description	Color Code	UOM
PBB0115	Standard	WHT, YEL, BLK, RED	Foot
PBB0115	Alternating	RW, BY	Foot
Part No.	Description	Color Code	Std. Pkg. Qty.
PBB0119	Standard	WHT, YEL, BLK, RED	100 ft.

**Master Link**

- Permanently joins separate lengths of chain

**S-Hooks**

- Open ends quickly link separate lengths of chain

**To Order Chain Accessories:** Add color code after part number.

Example: Part No. PBB0109 + Color Code WHT = PBB0109WHT

Part No.	Description	Color Code	UOM
PBB0109	Master Link Standard	WHT, YEL, BLK, RED	Each
PBB0138	S-Hook Standard	WHT, YEL, BLK, RED	Each

## Steel Safety Post &amp; Chain


Set out a sturdy post and chain system that stays in place.

**Steel Post**

- 2" dia. x 34" H powder-coated yellow steel
- 13.5" dia. base covered with durable, black ABS plastic
- Forged universal loop on top
- Indoor and outdoor use

**Steel Chain**

- Poly-coated yellow steel
- 2/0 straight link coil - 0.18" material dia., 1.29" inside length x 0.34" inside width (Maximum continuous length is 120 ft.)

**Bolt Snap**

- 4" nickel-plated cast zinc
- Double-ended

Part No.	Description	UOM
PBB0164	Steel Post	Each
PBB0057	Bolt Snap	Each
PBB0123	Poly-Coated Steel Chain	Foot



## Retractable Banner Barrier



Convey safety or warning messages with bold barriers.

- 0.060" aluminum roller housing holds 40"H x 54"W poly-vinyl banner
- Total viewable area: 32"H x 54"W
- Banner housing connects to Stanchion Posts via (2) paddle sleeves (included) that insert into interchangeable accessory caps (2 included)
- Sets up and breaks down easily

UOM
Each



PBB0027



PBB0028

## Rack Mount Retractable Belt Tape Barriers

Extend belt tape from the end of a storage rack.

- Mount with choice of hose clamp for semi-permanent installation or magnet for quick install and removal
- Durable 2" wide belt tape end has S-Clip to wrap and secure
- Yellow case with diagonal yellow/black striped tape or 'Caution' message tape



**To Order:** Add belt style code after part number. Black/Yellow – BY, Caution – C  
Example: Part No. PBB0006 + Belt Style Code BY = PBB0006BY

Hose Clamp			Magnetic Mount		
Part No.	UOM	Belt Length	Part No.	UOM	Belt Length
PBB0006	Each	15-ft.	PBB0007	Each	15-ft.
PBB0009	Each	20-ft.	PBB0011	Each	20-ft.
PBB0013	Each	25-ft.	PBB0015	Each	25-ft.



## Retractable Belt Tape Barriers



Connect belt tape in any combination of posts and wall mounts to control pedestrian traffic indoors.

### Belt Tape:

- Woven-polyester tape, wound in a self-tension, spring-loaded unit
- 2"W tape extends up to 8-ft – with straight tension without sag or slack
- Retracts smoothly back into the head unit for storage
- Safety mechanism in the spring-tension reduces the whip action of the belt braking, in case of accidental release

### Post Barriers:

- 2 1/2" dia. x 38"H with 14" dia. weighted base
- Available as Post Barrier with Belt Tape or as Receiver Posts (do not contain belt tape)

**To Order Post Barriers:** Add belt tape color code after Post Barriers part number: Black – BLK, Yellow – YEL, Red – RED.  
Example: Part No. PBB0177 + Color Code BLK = PBB0177BLK

Part No.	Post Color	UOM
PBB0177	Brushed Steel	Each
PBB0178	Black	Each
PBB0179	Yellow	Each

### Receiver Posts Only (Without Belt Tape)

Part No.	Post Color	UOM
PBB0181STL	Brushed Steel	Each
PBB0181BLK	Black	Each
PBB0181YEL	Yellow	Each

## Wall Mount Retractable Belt Tape Barriers

### Close off doorways or hallways.

- 2"W woven-polyester tape, wound in self-tension, spring-loaded unit
- Extends up to 8-ft. without sagging, retracts smoothly
- Head unit with bracket installs with four screws
- Wall Mount Receiver (sold separately) connects end of belt tape to facing wall



**To Order:** Add belt tape color code after part number:

Black – BLK, Yellow – YEL, Red – RED.

Example: Part No. PBB0045 + Color Code YEL = PBB0045YEL

Part No.	Case Color	UOM
PBB0045	Brushed Steel	Each
PBB0043	Black	Each
PBB0049	Yellow	Each

Wall Mount Receiver

Part No.	UOM
PBB0172	Each



## Outdoor Retractable Belt Tape Barriers

### Sturdy aluminum stanchion is ideal for use outdoors and in tough indoor environments


- 2 1/2" diameter aluminum post measures 40" high with a sturdy 14" diameter base
- Uses rust-proof stainless steel hardware
- Belt top has 2" wide retractable belt tape with ergonomic, rounded corner belt end and noticeable red slide action lock
- Can accept up to 3 additional belt ends from other belt tape posts
- Available with either 10-ft. or 15-ft. belt tape with contrasting black and yellow hazard stripes.
- Receiver Posts available separately

Part No.	Description	UOM
PBB0001	Black Post, Head, & Base	Each
PBB0002	Yellow Post, Black Head & Base	Each

### Aluminum Receiver Posts

Accepts up to 4 belts. Does not contain belt tape.

Part No.	Description	UOM
PBB0124	Black	Each
PBB0125	Yellow	Each



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PBB0023](#)