

Key panel - BT03AM/722070 S00001 - 2400592

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Key panel with 7.6 cm/3" FSTN-display (Without touch technology), 5 grayscales, ARM9™, 200 MHz, 2x USB host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows CE 5.0 and user software: TSvisRT. (bus system: PROFIBUS DP)

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 098654
GTIN	4055626098654

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

External dimension, width	144 mm
External dimension, height	96 mm
External dimension, depth	5 mm
Note regarding external dimension	Dimensions of the front plate
Installation dimension, width	136 mm
Installation dimension, height	82 mm
Installation dimension, depth	58 mm
Note regarding installation dimension	Mounting cutout, depth with bus if bus system present in the device

Display

Display	7.6 cm/3" FSTN
Screen resolution	160 x 80 Pixel(s)
Backlighting	LED
Display backlight MTBF	50000 h
Touch technology	Without touch technology

Key panel - BT03AM/722070 S00001 - 2400592

Technical data

Display

Colors	5 grayscales
--------	--------------

Computer data

Processor	ARM9™, 200 MHz
Operating system	Windows® CE 5.0
User software	TSvisRT
RAM	64 MB SDRAM
	512 KB SRAM
Mass storage	NOR-Flash, 32 MB
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x USB host 2.0
Bus system	PROFIBUS DP
Optional interfaces	none
Realtime clock	Yes
Service life of battery	5 years (typical)

General

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated
Mounting type	Front installation
Weight	500 g

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 %
Vibration (operation)	1g, according to EN 60068-2-6
Shock	15g, according to IEC 60068-2-27

Device supply

Typical current consumption	0.25 A
Power supply unit	24 V DC ±20 %

Standards and Regulations

Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 15;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Key panel - BT03AM/722070 S00001 - 2400592

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approval details

UL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> FILE E 205795

cUL Listed



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> FILE E 205795

cULus Listed



Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2400592](#)