18-26 AWG: WTB

00-9296



AVX continues to develop innovative connectors for the industrial electronics market that provide significant benefits over existing, outdated connector solutions. Listening to the design engineering community, there are ongoing applications where they cannot find an off-the-shelf solution that will satisfy a high percentage of the projects configuration, performance and cost goals.

The newest addition to AVX's broadening line of Wire-to-Board (WTB) connectors offers a cost effective, single Poke-Home connector solution that will meet the cost and performance targets in demanding, yet user friendly applications. At the heart of the connector is the industry proven dual tine, 3mm high spring force box contact that has been on the market as a standalone horizontal contact only solution.

The new SMT vertical through board connector allows for 18AWG to 26AWG wires to be simply stripped and inserted into the connector body at 180 degree orientation to the bottom side of the PCB with an above board height of 0.80mm. This single connector will replace existing 2-Piece WTB solutions where a header is soldered onto the PCB and a secondary crimp-to-wire receptacle assembly is plugged in. Available in 1-6 positions, each connector will accept the entire wire gauge range for either solid or stranded wires at varying current ratings supported by each wire size. Once inserted, wires can easily be removed or replaced by twisting/unscrewing or by using a small blade extraction tool.

APPLICATIONS

- Industrial/Ruggedized Wire-to-Board applications
- Replace hard soldering of wire to a PCB
- Replace costly 2-Piece header and receptacle products
- Reference Product Specification 201-01-151
- Reference Application Notes 201-01-152

FEATURES AND BENEFITS

- Dual Beam box contact provides maximum mechanical stability and wire retention
- Tape and reel packaged for automated SMT placement
- Will accept either solid or stranded wire, 18-26AWG, plated or un-plated wires
- · Simple strip and insert for wire loading, with easy twist and pull for wire removal

ELECTRICAL

Voltage Rating: 600 VAC 1 way 300 VAC 2 - 6 way

• Current Rating: See matrix below


ENVIRONMENTAL


 Operating Temperature: -40°C to +125°C


MECHANICAL

- Contact Material: Copper Alloy
- · Contact Plating: Tin over Nickel
- Durability: 5 Cycles

HOW TO ORDER







503



9 = UL White (Standard) 8 = UL Black (Special Order)

One Way Only (Special Order)

2 = Ul Brown

3 = UL Blue

4 = UL Yellow 5 = UL Red

6 = Ul Green

7 = UL Orange







CURRENT RATING

18AWG	20AWG	22AWG	24AWG	26AWG
7A	6A	5A	4A	3A


Certification: UL File #E90723

18-26 AWG: WTB




00-9296


9296 THROUGH BOARD MOUNT POKE HOME CONNECTOR 1 WAY














NOTES:

- 1. THROUGH BOARD SMT MOUNT 1 WAY POKE HOME CONNECTOR. FOR FURTHER DETAILS REFER TO PRODUCT SPECIFICATION 201-01-151 AND APPLICATION NOTES 201-01-152.
- 2. SUITABLE FOR WIRES 18AWG TO 26AWG. MAXIMUM INSULATION 2.20MM DIAMETER.
- 3. INSULATOR: NYLON 46, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 101.
- 4. CONTACT: TIN PLATED COPPER ALLOY.
- 5. PACKING IN TAPE AND REEL, QTY. PER REEL 400, 330MM REEL.
- 6. GENERAL TOLERANCE ±0.20.
- 7. CLEARANCE HOLE FOR CONNECTOR.
- 8. UL REFERENCE E90723.

SUGGESTED PCB LAYOUT









18-26 AWG: WTB





00-9296


9296 THROUGH BOARD MOUNT POKE HOME CONNECTOR 2 WAY













NOTES:

- 1. THROUGH BOARD SMT MOUNT 2 WAY POKE HOME CONNECTOR. FOR FURTHER DETAILS REFER TO PRODUCT SPECIFICATION 201-01-151 AND APPLICATION NOTES 201-01-152.
- $2. \ \ \text{SUITABLE FOR WIRES 18AWG TO 26AWG. MAXIMUM INSULATION 2.20MM DIAMETER.}$
- 3. INSULATOR: NYLON 46, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 101.
- 4. CONTACT: TIN PLATED COPPER ALLOY.
- 5. PACKING IN TAPE AND REEL, QTY. PER REEL 400, 330MM REEL.
- 6. GENERAL TOLERANCE ±0.20.
- 7. CLEARANCE HOLE FOR CONNECTOR.
- 8. UL REFERENCE E90723.

SUGGESTED PCB LAYOUT







18-26 AWG: WTB





00-9296


9296 THROUGH BOARD MOUNT POKE HOME CONNECTOR 3 WAY













NOTES:

- 1. THROUGH BOARD SMT MOUNT 3 WAY POKE HOME CONNECTOR. FOR FURTHER DETAILS REFER TO PRODUCT SPECIFICATION 201-01-151 AND APPLICATION NOTES 201-01-152.
- 2. SUITABLE FOR WIRES 18AWG TO 26AWG. MAXIMUM INSULATION 2.20MM DIAMETER.
- 3. INSULATOR: NYLON 46, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 101.
- 4. CONTACT: TIN PLATED COPPER ALLOY.
- 5. PACKING IN TAPE AND REEL, QTY. PER REEL 400, 330MM REEL.
- 6. GENERAL TOLERANCE ±0.20.
- 7. CLEARANCE HOLE FOR CONNECTOR.
- 8. UL REFERENCE E90723.

SUGGESTED PCB LAYOUT







18-26 AWG: WTB




00-9296


9296 THROUGH BOARD MOUNT POKE HOME CONNECTOR 4 WAY













NOTES:

- 1. THROUGH BOARD SMT MOUNT 4 WAY POKE HOME CONNECTOR. FOR FURTHER DETAILS REFER TO PRODUCT SPECIFICATION 201-01-151 AND APPLICATION NOTES 201-01-152.
- 2. SUITABLE FOR WIRES 18AWG TO 26AWG. MAXIMUM INSULATION 2.20MM DIAMETER.
- 3. INSULATOR: NYLON 46, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 101.
- 4. CONTACT: TIN PLATED COPPER ALLOY.
- 5. PACKING IN TAPE AND REEL, QTY. PER REEL 400, 330MM REEL.
- 6. GENERAL TOLERANCE ±0.20.
- 7. CLEARANCE HOLE FOR CONNECTOR.
- 8. UL REFERENCE E90723.

SUGGESTED PCB LAYOUT






18-26 AWG: WTB



00-9296

9296 THROUGH BOARD MOUNT POKE HOME CONNECTOR 5 WAY




PICK AND PLACE 2. Imm DIAMETER


NOTES:

- 1. THROUGH BOARD SMT MOUNT 5 WAY POKE HOME CONNECTOR. FOR FURTHER DETAILS REFER TO PRODUCT SPECIFICATION 201-01-151 AND APPLICATION NOTES 201-01-152.
- 2. SUITABLE FOR WIRES 18AWG TO 26AWG. MAXIMUM INSULATION 2.20MM DIAMETER.
- 3. INSULATOR: NYLON 46, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 101.
- 4. CONTACT: TIN PLATED COPPER ALLOY.
- 5. PACKING IN TAPE AND REEL, QTY. PER REEL 400, 330MM REEL.
- 6. GENERAL TOLERANCE ±0.20.
- 7. CLEARANCE HOLE FOR CONNECTOR.
- 8. UL REFERENCE E90723.

PACKING DETAILS



SUGGESTED PCB LAYOUT





18-26 AWG: WTB





00-9296

9296 THROUGH BOARD MOUNT POKE HOME CONNECTOR 6 WAY










PICK AND PLACE 2. Imm DIAMETER


NOTES:

- 1. THROUGH BOARD SMT MOUNT 6 WAY POKE HOME CONNECTOR. FOR FURTHER DETAILS REFER TO PRODUCT SPECIFICATION 201-01-151 AND APPLICATION NOTES 201-01-152.
- 2. SUITABLE FOR WIRES 18AWG TO 26AWG. MAXIMUM INSULATION 2.20MM DIAMETER.
- 3. INSULATOR: NYLON 46, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 101.
- 4. CONTACT: TIN PLATED COPPER ALLOY.
- 5. PACKING IN TAPE AND REEL, QTY. PER REEL 400, 330MM REEL.
- 6. GENERAL TOLERANCE ±0.20.
- 7. CLEARANCE HOLE FOR CONNECTOR.
- 8. UL REFERENCE E90723.

PACKING DETAILS

SUGGESTED PCB LAYOUT






18-26 AWG: WTB




00-9296

9296 THROUGH BOARD MOUNT POKE HOME CONNECTOR ASSEMBLY



THROUGH BOARD MOUNT POKE HOME CONNECTOR WIRE EXTRACTION TOOL



06-9296-7003-01-000 - PLASTIC TOOL 06-9296-7004-03-000 - METAL TOOL

Refer to application notes 201-01-152 for full wire extraction procedure.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AVX:

<u>009296002503906</u> <u>009296005503906</u> <u>009296003503906</u> <u>009296001503906</u> <u>009296006503906</u> 009296004503906 009296001503406 009296001503206 009296001503806