



Main

Range of product	Zelio Relay
Product or component type	Solid state relay
Device short name	SSP
Mounting support	Panel
Phase	3 phases
Contacts type and composition	3 NO
Solid state output type	Random voltage switching

Complementary

Control type	Without test button
[Uc] control circuit voltage	180...280 V AC
Minimum switching voltage	180 V AC turn-on
Maximum switching voltage	10 V AC turn-off
Response time	30 ms turn-off 20 ms turn-on
Input current limits	7...20 mA
Output voltage	48...530 V AC
Load current	0.1...25 A
Absolute maximum voltage	1200 V
Surge current	<= 275 A 20 ms <= 300 A 16.6 ms <= 85 A 1 s
Maximum I ² t for fusing	380 A ² .s 10 ms at 50 Hz half cycle 370 A ² .s 8.3 ms at 60 Hz half cycle
Leakage current	<= 3 mA off-state
Voltage drop	<= 1.35 V on-state
DV/dt	500 V/μs off-state at maximum voltage
Cos phi	>= 0.5 with maximum load
Motor power hp	0.75 hp at 104 °F (40 °C) 120 V AC 1 hp at 104 °F (40 °C) 240 V AC 3 hp at 104 °F (40 °C) 480 V AC 4.4 hp at 104 °F (40 °C) 530 V AC
Motor power kW	0.56 kW at 104 °F (40 °C) 120 V AC 0.74 kW at 104 °F (40 °C) 240 V AC 2.22 kW at 104 °F (40 °C) 480 V AC 3.24 kW at 104 °F (40 °C) 530 V AC
Insulation resistance	>= 1000 MOhm at 500 V DC
Capacitance unbalance	<= 8 pF input/output
Dielectric strength	4 kV AC input/output 4 kV AC input or output to case
Tightening torque	0.9...1.1 N.m input 1.7...2.2 N.m output
Connections - terminals	Screw terminals : 1 x 0.2...1 x 2.5 mm ² , (AWG 24...AWG 14) input Screw terminals : 1 x 1.5...1 x 10 mm ² , (AWG 16...AWG 8) output
Thermal resistance	0.24 °C/W
Local signalling	LED, green input
IP degree of protection	IP20
Product weight	0.79 lb(US) (0.36 kg)
Width	101.3 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SSP3A225P7R](#)