


4

3


2

1



LOC G	DIST 02	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			F3	REVISED PER ECO-11-004917	11MAR11	RK	HMR



- 1 MATING TAB THICKNESS .032
- 2 ASTERISK \* FOR PHOS. BRONZE ITEMS ONLY.
- 3 WIRE INSULATION DIA TO BE .170 MAX.
- 4 MAX RECOMMENDED OPERATING TEMP IS 105°C OR 221°F.
- 5 VOLTAGE RATING IS 300V MAX
- 6 CIRCULAR MIL AREA 1.0-2.5mm2 [1973-4934].



PHOS BRONZE ELECTRO-TIN 2	9-160463-5
BRASS ELECTRO-TIN	9-160463-2
DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth CHK T MICHIELUTTI APVD T MICHIELUTTI PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		11JUL05 11JUL05 11JUL05		<div>TE Connectivity</div>							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME  250 SERIES P.I.D.G. FASTON REC, ASS'Y, PIGGYBACK WIRE SIZE : 16-14 AWG									
		0 PLC ± — 1 PLC ± — 2 PLC ± .02 3 PLC ± .005 4 PLC ± — ANGLES ± 0°30'		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL  —		FINISH  —		A3		00779		C-160463		—			
CUSTOMER DRAWING								SCALE 5:1		SHEET 1 OF 1		REV F3	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9-160463-2](#)