





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A5	REVISED PER ECO-13-010026	21JUN2013	DLD	CJS
	A6	REVISED PER ECO-14-015042	03OCT2014	DLD	CJS
	A7	REVISED PER ECO-15-004219	08APR2015	DLD	CJS

- ⚠ MATERIAL: BRASS
- ⚠ FINISH: PRE-PLATED WITH 0.80µm MIN TIN
- ⚠ MATERIAL ID FEATURE IN "DOWN" POSITION.
4. THE INTENDED TEMPERATURE RANGE FOR THIS TERMINAL IS -40° C TO 100° C.
- ⚠ NOT FOR SEALED APPLICATIONS.



SECTION S-S
SCALE 20:1



SECTION N-N
SCALE 20:1

0.13mm ² = 0.85-1.05	DETAIL B	1.40	2.40	0.80	1.85	⚠	2X 0.13mm ²	1924968-8 ⚠
0.35mm ² = 1.10-1.40							0.35mm ²	
0.85-1.05	DETAIL B	0.85	1.82	0.65	1.50	⚠	26 [0.13mm ²]	1924968-7 ⚠
0.13mm ² = 0.85-1.05	DETAIL A	1.40	2.40	0.80	1.85	⚠	2X 0.13mm ²	1924968-6 ⚠
0.35mm ² = 1.10-1.40							0.35mm ²	
0.85-1.05	DETAIL A	0.85	1.82	0.65	1.50	⚠	26 [0.13mm ²]	1924968-5 ⚠
2.06 MAX	DETAIL B	1.78	2.94	1.00	1.96	⚠	18 [0.75mm ²]	1924968-4
1.50-1.85	DETAIL B	1.78	2.94	0.80	1.82	⚠	20-22 [0.5-0.35mm ²]	1924968-3
2.06 MAX	DETAIL A	1.78	2.94	1.00	1.96	⚠	18 [0.75mm ²]	1924968-2
1.50-1.85	DETAIL A	1.78	2.94	0.80	1.82	⚠	20-22 [0.5-0.35mm ²]	1924968-1
INSULATION DIAMETER	REELING	M	L	K	J	FINISH	WIRE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. MOLL CHK J. HALL APVD J. HALL	02OCT2008 02OCT2008 02OCT2008	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ±1°		PRODUCT SPEC 108-2296-1	
MATERIAL		FINISH		APPLICATION SPEC 114-13183	
-		-		WEIGHT	
-		-		CUSTOMER DRAWING	
-		-		SIZE A1	
-		-		CAGE CODE 00779	
-		-		DRAWING NO. 1924968	
-		-		RESTRICTED TO	
-		-		SCALE 10:1	
-		-		SHEET 1	
-		-		OF 1	
-		-		REV A7	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1924968-1](#)