



# 16A, 50V - 600V Isolated Glass Passivated High Efficient Rectifiers

#### **FEATURES**

- Glass passivated chip junction
- High efficiency, Low VF
- High surge current capability
- High current capability
- High reliability
- High surge current capability
- UL Recognized File # E-326243
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21

### **MECHANICAL DATA**

Case: ITO-220AC

Molding compound, UL flammability classification rating 94V-0

Part no. with suffix "H" means AEC-Q101 qualified

Packing code with suffix "G" means green compound (halogen-free) **Terminal:** Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 2 whisker test

Polarity: As marked

**Mounting torque:** 0.56 Nm max. **Weight:** 1.7 g (approximately)







PIN 1	0
PIN 2	0

**ITO-220AC** 

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T <sub>A</sub> =25°C unless otherwise noted)								
PARAMETER	CVMDOL	HERAF	HERAF	HERAF	HERAF	HERAF	HERAF	UNIT
PARAIVIETER	SYMBOL	1601G	1602G	1603G	1604G	1605G	1606G	
Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	200	300	400	600	V
Maximum RMS voltage	$V_{RMS}$	35	70	140	210	280	420	V
Maximum DC blocking voltage	$V_{DC}$	50	100	200	300	400	600	V
Maximum average forward rectified current	I <sub>F(AV)</sub>	16			Α			
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	250				А		
Maximum instantaneous forward voltage (Note 1) $I_F$ = 16 A	V <sub>F</sub>	1.0 1.3		1.7	V			
Maximum reverse current @ rated $V_R$ $T_J$ =25°C $T_J$ =125°C	I <sub>R</sub>	10 400			μΑ			
Maximum reverse recovery time (Note 2)	t <sub>rr</sub>	50 80					ns	
Typical junction capacitance (Note 3)	CJ	150 110					pF	
Typical thermal resistance	$R_{ heta JC}$	2				°C/W		
Operating junction temperature range	T <sub>J</sub>	- 55 to +150				°C		
Storage temperature range	T <sub>STG</sub>	- 55 to +150				°C		

Note 1: Pulse Test with PW=300µs, 1% duty cycle

Note 2: Test conditions:  $I_F$ =0.5A,  $I_R$ =1.0A,  $I_{RR}$ =0.25A

Note 3: Measured at 1 MHz and applied reverse voltage of 4.0V DC.



ORDERING INFORMATION							
PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX <sup>(*)</sup>	PACKAGE	PACKING		
HERAF160xG (Note 1)	Н	C0	G	ITO-220AC	50 / Tube		


Note 1: "x" defines voltage from 50V (HERAF1601G) to 600V (HERAF1606G)


<sup>\*:</sup> Optional available


EXAMPLE							
EXAMPLE P/N	PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION		
HERAF1601GHC0G	HERAF1601G	Н	CO	G	AEC-Q101 qualified Green compound		


#### **RATINGS AND CHARACTERISTICS CURVES**

(T<sub>A</sub>=25°C unless otherwise noted)












0

300 f=1.0MHz JUNCTION CAPACITANCE (pF) 250 Vsig=50mVp-p 200 HERAF1601G-05G 150 HERAF1606G 100 50


REVERSE VOLTAGE (V)

FIG. 5 TYPICAL JUNCTION CAPACITANCE

### FIG.6 REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM




1000



### **PACKAGE OUTLINE DIMENSIONS ITO-220AC**

10



DIM.	Unit	(mm)	Unit (inch)		
DIIVI.	Min	Max	Min	Max	
Α	4.30	4.70	0.169	0.185	
В	2.50	3.10	0.098	0.122	
С	2.30	2.90	0.091	0.114	
D	0.46	0.76	0.018	0.030	
Е	6.30	6.90	0.248	0.272	
F	9.60	10.30	0.378	0.406	
G	3.00	3.40	0.118	0.134	
Н	0.00	1.60	0.000	0.063	
I	0.95	1.45	0.037	0.057	
J	0.50	0.90	0.020	0.035	
K	2.40	3.20	0.094	0.126	
L	14.80	15.50	0.583	0.610	
М	-	4.10	-	0.161	
N		1.80		0.071	
0	12.60	13.80	0.496	0.543	
Р	4.95	5.20	0.195	0.205	

### **MARKING DIAGRAM**



P/N = Specific Device Code G = Green Compound

YWW = Date Code F = Factory Code





#### **Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Version: J1512

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Taiwan Semiconductor:

HERAF1601G HERAF1602G HERAF1603G HERAF1604G HERAF1605G HERAF1606G HERAF1604G CO
HERAF1603G CO HERAF1602G CO HERAF1606G CO HERAF1605G CO HERAF1601G CO HERAF1605G COG