

High Voltage PNP Epitaxial Planar Transistor

SOT-223



Pin Definition:

1. Base
2. Collector
3. Emitter

PRODUCT SUMMARY

| | |
|---------------|--------------------------------|
| BV_{CBO} | -560V |
| BV_{CEO} | -560V |
| I_C | -150mA |
| $V_{CE(SAT)}$ | -0.5V @ $I_C=-50mA, I_B=-10mA$ |

Features

- Low Saturation Voltages
- High Breakdown Voltage

Structure

- Epitaxial Planar Type
- PNP Silicon Transistor

Ordering Information

| Part No. | Package | Packing |
|---------------|---------|--------------------|
| TSA1765CW RPG | SOT-223 | 2.5Kpcs / 13" Reel |

Note: "G" denotes for Halogen Free

Absolute Maximum Rating (Ta = 25°C unless otherwise noted)

| Parameter | Symbol | Limit | Unit |
|--|-----------|--------------|------|
| Collector-Base Voltage | V_{CBO} | -560 | V |
| Collector-Emitter Voltage | V_{CEO} | -560 | V |
| Emitter-Base Voltage | V_{EBO} | -7 | V |
| Collector Current | I_C | -150 | mA |
| Collector Current(Pulse) | I_{CP} | -500 | |
| Base Current | I_B | -50 | |
| Total Power Dissipation @ $T_C=25^\circ C$ | P_{tot} | 2 | W |
| Operating Junction Temperature | T_J | +150 | °C |
| Operating Junction and Storage Temperature Range | T_{STG} | - 55 to +150 | °C |

Electrical Specifications (Ta = 25°C unless otherwise noted)

| Parameter | Conditions | Symbol | Min | Typ | Max | Unit |
|--------------------------------------|-------------------------------|-----------------|------|-----|------|------|
| Collector-Base Breakdown Voltage | $I_C = -1mA, I_E = 0$ | BV_{CBO} | -560 | -- | -- | V |
| Collector-Emitter Breakdown Voltage | $I_C = -1mA, I_B = 0$ | BV_{CEO} | -560 | -- | -- | V |
| Emitter-Base Breakdown Voltage | $I_E = -10\mu A, I_C = 0$ | BV_{EBO} | -7 | -- | -- | V |
| Collector Cutoff Current | $V_{CB} = -560V, I_E = 0$ | I_{CBO} | -- | -- | -100 | nA |
| Emitter Cutoff Current | $V_{EB} = -7V, I_C = 0$ | I_{EBO} | -- | -- | -100 | nA |
| Collector-Emitter Saturation Voltage | $I_C = -20mA, I_B = -2mA$ | $V_{CE(SAT)} 1$ | -- | -- | -0.2 | V |
| | $I_C = -50mA, I_B = -10mA$ | $V_{CE(SAT)} 2$ | -- | -- | -0.5 | |
| Base-Emitter Saturation Voltage | $I_C = -50mA, I_B = -10mA$ | $V_{BE(SAT)} 1$ | -- | -- | -1.0 | V |
| Base-Emitter on Voltage | $V_{CE} = -10V, I_C = -50mA$ | $V_{BE(ON)}$ | -- | -- | -1.0 | V |
| DC Current Transfer Ratio | $V_{CE} = -10V, I_C = -1mA$ | $h_{FE} 1$ | 150 | -- | -- | |
| | $V_{CE} = -10V, I_C = -50mA$ | $h_{FE} 2$ | 80 | -- | 300 | |
| | $V_{CE} = -10V, I_C = -100mA$ | $h_{FE} 3$ | -- | 15 | -- | |
| Transition Frequency | $V_{CE} = -20V, I_E = -10mA$ | f_T | 50 | -- | -- | MHz |
| Output Capacitance | $V_{CB} = -20V, f = 1MHz$ | C_{ob} | -- | -- | 8 | pF |

Electrical Characteristics Curve ($T_a = 25^\circ\text{C}$, unless otherwise noted)

Figure 1. Static Characteristics




Figure 2. DC Current Gain




Figure 3. VCE(SAT) v.s. VBE(SAT)




Figure 4. Power Derating






Figure 5. Safety Operation Area




SOT-223 Mechanical Drawing



Unit: Millimeters

Marking Diagram



Y = Year Code

M = Month Code for Halogen Free Product

O =Jan **P** =Feb **Q** =Mar **R** =Apr

S =May **T** =Jun **U** =Jul **V** =Aug

W =Sep **X** =Oct **Y** =Nov **Z** =Dec

L = Lot Code

Not Recommended

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[TSA1765CW RP](#)