



REV	DESCRIPTIONS	DATE	APPROVED
N/C	NEW RELEASE PER E.O.H4348	6/8/07	M.A.
A	REVISED PER E.O.H4394	12/6/07	M.A.



1. DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.
 2. INSERT ARRANGEMENT PER MIL-STD-1669.
 3. LEAK RATE: $< 1 \text{E-}8$ cc/sec He @ 1 atm.
 4. INSULATION RESISTANCE: > 5000 MEGOHM @ 500 VDC
DIELECTRIC WITHSTANDING VOLTAGE: NO BREAKDOWN @ 2300 VAC
 5. MATERIAL:
SHELL/HEX NUT - 304L STAINLESS STEEL
INSULATOR - GLASS INSERT
CONTACT - 52 HIGH NICKEL-IRON ALLOY
INTERFACIAL SEAL- SILICONE ELASTOMER
O-RING - NITRILE OR BUNA N
 6. FINISH:
SHELL - PASSIVATION
HEX NUT - NICKEL PER QQ-N-290
CONTACT - GOLD OVER NICKEL
 7. THIS CONNECTOR IS SIMILAR TO 46108-20-16PN EXCEPT LESS 2 KEYWAYS.
- NOTE(S):

 $\phi .817^{+.010}_{-.005}$ RECOMMENDED
PANEL CUT-OUT

FILE:46136-20-16P3-ENV

	SIGNATURE & DATE
DR	S.LUI 6/7/07
CHK	M.ALLEN 6/8/07
PE	T.SERENO 6/8/07
APPD	A.RENGIFO 6/8/07
SCALE:	

RECEPTACLE CONNECTOR
HERMETIC
SINGLE HOLE MT
BAYONET COUPLING
HEAVY DUTY 20-16 ARR
MIL-C-26482 TYPE
SPECIAL CLOCKING
ENVELOPE

CP	MATL CODE 73
DEUTSCH ENGINEERED INTERCONNECT SOLUTIONS 250 Eddie Jones Way Oceanside, CA 92054	
B DWG SIZE	46136-20-16P3 CAGE CODE 11139
SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[46136-20-16P3](#)