

D

C

B





A

D

C

B

A



1 MATERIAL: HOUSING - UL 94V-O RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS
HOLDDOWNS - PHOSPHOR BRONZE.

2 RECOMMENDED PC BOARD THICKNESS OF 1.57.

3 KAPTON VACUUM PICK UP BUTTON.

4 PLATING: CONTACTS - 0.38µm MINIMUM GOLD ON MATING AREA,
2.54µm MINIMUM MATTE TIN ON SOLDER TAILS,
ALL OVER 1.27µm MINIMUM NICKEL.
HOLDDOWNS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.

5 COUNTERPART RECOMMENDED IS PN 1445022 OR 2008571 (DASH ACC. TO NUMBER OF POSITION).

6 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE

33.00	40.27	40.00	12	3-1445087-2
30.00	37.27	37.00	11	3-1445087-1
27.00	34.27	34.00	10	3-1445087-0
24.00	31.27	31.00	9	2-1445087-9
21.00	28.27	28.00	8	2-1445087-8
18.00	25.27	25.00	7	2-1445087-7
15.00	22.27	22.00	6	2-1445087-6
12.00	19.27	19.00	5	2-1445087-5
9.00	16.27	16.00	4	2-1445087-4
6.00	13.27	13.00	3	2-1445087-3
3.00	10.27	10.00	2	2-1445087-2
DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
J. ROOT
09OCT2000

CHK
K. WHITAKER
20-FEB-2001

APVD
C. JONES
20-FEB-2001

TE Connectivity

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.20
3 PLC ±
4 PLC ±
ANGLES ±1°
FINISH

PRODUCT SPEC
108-1836

APPLICATION SPEC
114-13000

WEIGHT
-

NAME
VERTICAL SURFACE MOUNT HEADER ASSY,
15 MIC GOLD CONTACTS,SURFACE MOUNT,
HOLDDOWNS, SGL ROW,MICRO MATE-N-LOK™

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-1445087


RESTRICTED TO
-

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 2

REV D6



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1445087-5](#)