

© 2020 TE Connectivity. All Rights Reserved.

TE NO.	POSN	A	B	C	D	E	F	COLOR
1456315-1	24	7.50	12.00	9.00	9.00	39.2	35,5	BLACK
1456315-2	24	7.50	11.00	11.00	9.00	39.2	35,5	BLACK
1456315-3	24	7.50	11.00	11.00	12.00	39.2	35,5	GREY
1456315-4	24	9.00	11.00	11.00	9.00	39.2	35,5	GREY
1456315-5	32	12.00	12.00	12.00	9.00	49.2	45.5	BLACK
1456315-6	32	12.00	12.00	12.00	9.00	49.2	45.5	BLACK
1456315-7	24	7.50	11.00	11.00	12.00	39.2	35,5	GREY
1456315-8	24	9.00	11.00	11.00	9.00	39.2	35,5	GREY
1456315-9	24	7.50	11.00	11.00	12.00	39.2	35,5	GREY
1-1456315-0	24	7.50	11.00	11.00	12.00	39.2	35,5	GREY
1-1456315-1	24	9.00	11.00	11.00	9.00	39.2	35,5	GREY
1-1456315-2	24	9.00	11.00	11.00	9.00	39.2	35,5	GREY
1-1456315-3	24	7.50	12.00	9.00	9.00	39.2	35,5	BLACK
1-1456315-4	24	7.50	11.00	11.00	9.00	39.2	35,5	BLACK
1-1456315-5	24	7.50	11.00	11.00	12.00	39.2	35,5	GREY
1-1456315-6	24	9.00	11.00	11.00	9.00	39.2	35,5	GREY
1-1456315-7	24	9.00	11.00	11.00	9.00	39.2	35,5	GREY
1-1456315-8	24	7.50	11.00	11.00	12.00	39.2	35,5	GREY
1-1456315-9	24	9.00	11.00	11.00	9.00	39.2	35,5	GREY
2-1456315-0	32	12.00	12.00	12.00	9.00	49.2	45.5	BLACK

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F1	REVISED PER ECR-08-006840	17MAR2008	JM	JM
	G	REV PER ECO-10-0221116	29OCT2010	DD	DR
	G1	REVISED PER ECO-20-012739	29SEP2020	AP	GK

Part Number	SIZE	Complexity Matrix Position Number																																Not Applicable	×	
		Closed Position																																○	○	
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32			
1456315-1	24								○	○	○	○	○	○	○	○											×	×	×	×	×	×	×	×		
1456315-2	24								○	○	○	○	○	○	○	○											×	×	×	×	×	×	×	×		
1456315-3	24			○	○	○					○			○		○	○						○	○			×	×	×	×	×	×	×	×		
1456315-4	24		○		○	○				○	○				○	○	○	○			○	○	○	○			×	×	×	×	×	×	×	×		
1456315-5	32					○			○		○	○	○	○	○	○	○	○	○	○	○	○														
1456315-6	32					○				○	○	○	○	○	○	○	○	○	○	○	○								○	○						
1456315-7	24			○	○	○							○										○	○			×	×	×	×	×	×	×	×		
1456315-8	24		○		○	○					○				○	○	○	○			○	○	○	○			×	×	×	×	×	×	×	×		
1456315-9	24			○	○	○							○										○	○	○		×	×	×	×	×	×	×	×		
1-1456315-0	24			○	○	○							○					○				○	○	○		×	×	×	×	×	×	×	×			
1-1456315-1	24		○		○	○					○				○	○		○	○	○	○	○	○			×	×	×	×	×	×	×	×			
1-1456315-2	24		○		○	○					○	○			○	○	○	○	○	○	○	○	○			×	×	×	×	×	×	×	×			
1-1456315-3	24			○			○		○	○	○	○	○	○	○	○	○					○			×	×	×	×	×	×	×	×				
1-1456315-4	24			○			○		○	○	○	○	○	○	○	○	○					○	○		×	×	×	×	×	×	×	×				
1-1456315-5	24			○	○	○							○										○	○		×	×	×	×	×	×	×	×			
1-1456315-6	24		○		○	○		○		○		○			○	○	○	○	○	○	○	○	○			×	×	×	×	×	×	×	×			
1-1456315-7	24		○		○	○			○	○	○				○	○	○	○	○	○	○	○			×	×	×	×	×	×	×	×				
1-1456315-8	24			○	○	○																	○			×	×	×	×	×	×	×	×			
1-1456315-9	24			○	○		○	○	○						○	○	○		○	○	○	○			×	×	×	×	×	×	×	×				
2-1456315-0	32					○		○		○	○	○	○	○	○	○	○	○	○	○	○												○			

Recommended Terminal	
TE P/N	AWG
0-1437284-9	20-18
1-1437284-0	16

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08JUN2001 R. HARDISON	TE Connectivity	
DIMENSIONS: mm		CHK 08JUN2001 R. HARDISON	NAME SOCKET ASSY, FOR 1.0mm MIP CONN SYS SELECTIVELY LOADED STRAIN RELIEF SIEMENS AUTOMOTIVE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±1.0 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.070 4 PLC ±0.050 ANGLES ±2° FINISH -		APVD 08JUN2001 R. HARDISON	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL -		PRODUCT SPEC -	A200779C-1456315	
APPLICATION SPEC -		WEIGHT -	SCALE 2.000 SHEET 1 OF 1 REV G1	
CUSTOMER DRAWING				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1456315-6](#)