


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP(ECN-23-233124)	28SEP2023	ED	WH



NOTES:

- 1 PACK IN ACCORDANCE WITH TE SPEC 107-3275;
- 2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;
- 3 ELECTRICAL CHARACTERISTICS :
FREQUENCY RANGE : DC-18GHz
NOMINAL IMPEDANCE : 50 OHMS
POWER RATING: 2W
VSWR : 1.3 MAX(DC-18GHz)
- 4 MECHANICAL CHARACTERISTICS :
DURABILITY : 500 CYCLES
TORQUE SETTING : 7-10 IN-LBS;
- 5 TEMPERATURE RANGE: -40°-+125°;
- 6 RoHS: COMPLIANT.

	1	GOLD 1u"/ NICKEL/COPPER	BRASS	SHELL	8
	1	PASSIVATION	STAINLESS STEEL	RETAINER RING	7
	1	RED	SILICONE RUBBER	GASKET	6
	1	GOLD 1u"/ NICKEL/COPPER	BRASS	COVER	5
	1	NATURAL	50 OHM	RESISTOR	4
	1	GOLD 10u"/ NICKEL/COPPER	BERYLLIUM COPPER	CENTER CONTACT	3
	1	NATURAL	PTFE	INSULATOR	2
	1	GOLD 1u"/ NICKEL/COPPER	BRASS	BODY	1
	2467942-1	PLATING	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY		PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ED 28SEP2023	TE Connectivity		
DIMENSIONS: mm		CHK ED 28SEP2023			
		APVD WH 28SEP2023	NAME SMA MALE REVERSE POLARITY TERMINATION, STRAIGHT,18GHZ		
		PRODUCT SPEC	-		
		APPLICATION SPEC	-		
MATERIAL SEE TABLE		WEIGHT -	SIZE A2	CAGE CODE 00779	RESTRICTED TO -
		FINISH -	DRAWING NO C-2467942		
CUSTOMER DRAWING			SCALE 8:1	SHEET 1 OF 1	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2467942-1](#)