







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-20-005011	06APR2020	QY	JB
	C	ECR-20-007704	03JUN2020	QY	JB
	C1	ECR-20-016724	25NOV2020	QY	JB




NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250V
RATED CURRENT: 10A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4KV
POLLUTION DEGREE: 3
MATING CYCLES: 500 CYCLES
TEMPERATURE RANGE: $-40\sim+125^{\circ}C$
WIRE RANGE: $0.14mm^2\sim2.5mm^2$ (AWG26-AWG14)
2.CONTACT NEED TO BE ORDERED SEPARATELY.

注释:
1. 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 4KV
污染等级: 3
插拔次数: 500 次
温度范围: $-40\sim+125^{\circ}C$
接线范围: $0.14mm^2\sim2.5mm^2$ (AWG26-AWG14)
2. 端子需要单独订购.



PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS
不使用防护外壳时芯件的安装开孔图

2-1103113-3		HN.D.64.Bu.C		HD-064 FEMALE INSERT FOR MACHINED CONTACT TYPE HD-064 母插, 车削针型 (HTS)			
PART NUMBER 料 号		PART DESCRIPTION 描 述					
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09JAN2020 CHK QIANG YUAN JAN BREDOW APVD 09JAN2020 MARCIN KOMAR		 TE Connectivity NAME HN.D.64.Bu.C			
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- MATERIAL - FINISH -					PRODUCT SPEC 108-74002 APPLICATION SPEC 114-74000 WEIGHT -
		CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C=1103113	RESTRICTED TO -
				SCALE 3:2	SHEET 1 OF 1	REV C1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1103113-3](#)